

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774702

Luminaire Tested: LD6D95BD010-EU6DR6070959050-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959050-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11639.8 lumens
Efficiency: N/A
Efficacy: 117.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774702

CATALOG NUMBER: LD6D95BD010-EU6DR6070959050-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P774702

CATALOG NUMBER: LD6D95BD010-EU6DR6070959050-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	92		95	93	90		92	90	89
3	102	96	91	87		100	95	90	86		92	88	85		90	86	84		87	85	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	92	84	78	74		91	83	77	73		81	76	73		79	75	72		78	74	71
6	87	79	73	68		86	78	72	68		76	71	68		75	70	67		74	70	67
7	83	74	68	63		82	73	67	63		72	67	63		71	66	63		69	65	62
8	79	69	63	59		78	69	63	59		68	63	59		67	62	59		66	61	58
9	75	65	59	55		74	65	59	55		64	59	55		63	58	55		62	58	55
10	72	62	56	52		71	61	56	52		61	55	52		60	55	52		59	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1272713
5°	1269601
10°	1311773
15°	1313130
20°	1208215
25°	1027667
30°	783046
35°	553738
40°	325167
45°	131201
50°	43804
55°	21087
60°	8653
65°	1293
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 131201 cd/sqm



TEST NUMBER: P774702

CATALOG NUMBER: LD6D95BD010-EU6DR6070959050-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1116.7	9.6
10°-20°	3216.0	27.6
20°-30°	3849.2	33.1
30°-40°	2574.5	22.1
40°-50°	763.3	6.6
50°-60°	109.7	0.9
60°-70°	10.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8181.9	70.3
0°-40°	10756.3	92.4
0°-60°	11629.4	99.9
0°-90°	11639.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11639.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11648	
5°	11576	###
15°	11609	3216
25°	8524	3849
35°	4152	2574
45°	849	763
55°	111	110
65°	5	10
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774702

CATALOG NUMBER: LD6D95BD010-EU6DR6070959050-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

0°	
0°	11648.4
2.5°	11633.5
5°	11575.7
7.5°	11732.7
10°	11823.5
12.5°	11807.0
15°	11608.8
17.5°	11141.2
20°	10391.2
22.5°	9490.9
25°	8524.4
27.5°	7435.8
30°	6206.6
32.5°	5109.7
35°	4151.5
37.5°	3191.7
40°	2279.8
42.5°	1503.3
45°	849.1
47.5°	434.5
50°	257.7
52.5°	166.9
55°	110.7
57.5°	71.0
60°	39.6
62.5°	16.5
65°	5.0
67.5°	1.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)