

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202519

Luminaire Tested: **LD6B20D010 EU6B10209024 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202519
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209024 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1541.9 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202519

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSWMH1

Luminous Intensity Polar Plot






TEST NUMBER: P202519

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	111	107	104	101		108	105	102	99		101	98	96			97	95	93			88
2	103	96	90	85		100	94	89	84		91	86	82			87	84	81			77
3	95	86	79	73		92	84	78	73		81	76	71			79	74	70			67
4	88	77	70	64		86	76	69	63		74	67	62			71	66	62			59
5	81	70	62	56		79	69	61	56		67	60	55			65	59	55			52
6	76	64	56	50		74	63	55	50		61	54	49			59	53	49			47
7	70	58	50	45		69	57	50	45		56	49	44			55	48	44			42
8	66	54	46	40		64	53	45	40		52	45	40			50	44	40			38
9	62	49	42	37		61	49	42	37		48	41	37			47	41	36			35
10	58	46	39	34		57	45	38	34		45	38	34			44	38	33			32

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202519

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	82.5	5.4
10°-20°	215.6	14.0
20°-30°	285.9	18.5
30°-40°	305.0	19.8
40°-50°	285.1	18.5
50°-60°	217.4	14.1
60°-70°	118.3	7.7
70°-80°	31.7	2.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.1	37.9
0°-40°	889.1	57.7
0°-60°	1391.6	90.2
0°-90°	1541.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1541.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	892	
5°	879	82
15°	769	216
25°	622	286
35°	487	305
45°	371	285
55°	245	217
65°	118	118
75°	27	32
85°	0	0
90°	0	



TEST NUMBER: P202519

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	891.6
2.5°	888.8
5°	879.4
7.5°	859.5
10°	836.9
12.5°	804.7
15°	768.8
17.5°	733.0
20°	694.2
22.5°	657.4
25°	622.4
27.5°	585.6
30°	550.7
32.5°	516.7
35°	487.4
37.5°	458.1
40°	427.9
42.5°	400.5
45°	371.2
47.5°	339.1
50°	308.9
52.5°	276.7
55°	244.6
57.5°	209.7
60°	177.6
62.5°	147.3
65°	118.1
67.5°	91.6
70°	67.1
72.5°	46.3
75°	27.4
77.5°	12.3
80°	2.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)