

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774315

Luminaire Tested: LD6D95BD010-EU6DR3570959050-6LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774315
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR3570959050-6LBDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9847.5 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774315

CATALOG NUMBER: LD6D95BD010-EU6DR3570959050-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P774315

CATALOG NUMBER: LD6D95BD010-EU6DR3570959050-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96		
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92		
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88		
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84		
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81		
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78		
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75		
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72		
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70		
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2960464
5°	2890907
10°	2605473
15°	2022260
20°	1146997
25°	446238
30°	166473
35°	91247
40°	59648
45°	36296
50°	23100
55°	16325
60°	11953
65°	6489
70°	479
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36296 cd/sqm



TEST NUMBER: P774315

CATALOG NUMBER: LD6D95BD010-EU6DR3570959050-6LBPD1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2424.2	24.6
10°-20°	4733.0	48.1
20°-30°	1930.3	19.6
30°-40°	461.9	4.7
40°-50°	192.5	2.0
50°-60°	79.7	0.8
60°-70°	25.0	0.3
70°-80°	0.6	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9087.5	92.3
0°-40°	9549.4	97.0
0°-60°	9821.6	99.7
0°-90°	9847.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9847.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	27095	
5°	26358	###
15°	17878	4733
25°	3702	1930
35°	684	462
45°	235	192
55°	86	80
65°	25	25
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P774315

CATALOG NUMBER: LD6D95BD010-EU6DR3570959050-6LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	27095.4
2.5°	26932.9
5°	26358.1
7.5°	25211.4
10°	23484.1
12.5°	21051.9
15°	17877.9
17.5°	13996.2
20°	9864.7
22.5°	6290.3
25°	3701.5
27.5°	2092.3
30°	1319.5
32.5°	926.5
35°	684.1
37.5°	529.0
40°	418.2
42.5°	322.1
45°	234.9
47.5°	175.8
50°	135.9
52.5°	107.9
55°	85.7
57.5°	69.4
60°	54.7
62.5°	39.9
65°	25.1
67.5°	8.9
70°	1.5
72.5°	1.5
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)