

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204265

Luminaire Tested: **LD6B20D010 EU6B10208027 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204265
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208027 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2041.9 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204265

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBSWH1

Luminous Intensity Polar Plot






TEST NUMBER: P204265

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101	108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85	100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73	93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64	86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56	79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50	74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45	69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41	65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37	61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34	57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204265

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.3	5.5
10°-20°	290.7	14.2
20°-30°	380.3	18.6
30°-40°	402.6	19.7
40°-50°	375.5	18.4
50°-60°	284.4	13.9
60°-70°	154.1	7.5
70°-80°	41.3	2.0
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	783.3	38.4
0°-40°	1185.9	58.1
0°-60°	1845.9	90.4
0°-90°	2041.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2041.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1218	
5°	1200	112
15°	1039	291
25°	827	380
35°	644	403
45°	489	376
55°	320	284
65°	154	154
75°	36	41
85°	0	1
90°	0	



TEST NUMBER: P204265

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1217.8
2.5°	1213.3
5°	1199.9
7.5°	1170.9
10°	1132.9
12.5°	1088.2
15°	1039.0
17.5°	983.2
20°	934.0
22.5°	878.1
25°	826.8
27.5°	775.4
30°	726.2
32.5°	683.7
35°	643.5
37.5°	603.3
40°	565.3
42.5°	527.3
45°	489.3
47.5°	446.9
50°	404.4
52.5°	362.0
55°	319.5
57.5°	274.8
60°	232.4
62.5°	192.2
65°	154.2
67.5°	118.4
70°	87.1
72.5°	60.3
75°	35.8
77.5°	15.6
80°	4.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)