

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202514

Luminaire Tested: **LD6B20D010 EU6B10208027 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208027 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2041.9 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202514

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBSWMH1

Luminous Intensity Polar Plot






TEST NUMBER: P202514

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	82		87	84	81		84
3	95	86	79	73	92	84	78	73	81	76	71		79	74	70		76
4	88	77	70	64	86	76	69	63	74	67	62		71	66	62		69
5	81	70	62	56	79	69	61	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		59	53	49		58
7	70	58	50	45	69	57	50	45	56	49	44		55	48	44		53
8	66	54	46	40	64	53	45	40	52	45	40		50	44	40		49
9	62	49	42	37	61	49	42	37	48	41	37		47	41	36		46
10	58	46	39	34	57	45	38	34	45	38	34		44	38	33		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202514

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.2	5.3
10°-20°	285.6	14.0
20°-30°	378.7	18.5
30°-40°	403.9	19.8
40°-50°	377.5	18.5
50°-60°	287.9	14.1
60°-70°	156.6	7.7
70°-80°	42.0	2.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	773.5	37.9
0°-40°	1177.4	57.7
0°-60°	1842.8	90.2
0°-90°	2041.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2041.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1181	
5°	1164	109
15°	1018	286
25°	824	379
35°	645	404
45°	492	378
55°	324	288
65°	156	157
75°	36	42
85°	0	1
90°	0	



TEST NUMBER: P202514

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1180.8
2.5°	1177.0
5°	1164.5
7.5°	1138.2
10°	1108.2
12.5°	1065.7
15°	1018.2
17.5°	970.6
20°	919.3
22.5°	870.6
25°	824.3
27.5°	775.5
30°	729.2
32.5°	684.2
35°	645.4
37.5°	606.6
40°	566.6
42.5°	530.3
45°	491.6
47.5°	449.0
50°	409.0
52.5°	366.5
55°	324.0
57.5°	277.7
60°	235.2
62.5°	195.1
65°	156.4
67.5°	121.3
70°	88.8
72.5°	61.3
75°	36.3
77.5°	16.3
80°	3.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)