

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774630

Luminaire Tested: LD6D95BD010-EU6DR5570959050-6LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774630
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5570959050-6LBDP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11150.0 lumens
Efficiency: N/A
Efficacy: 112.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774630

CATALOG NUMBER: LD6D95BD010-EU6DR5570959050-6LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P774630

CATALOG NUMBER: LD6D95BD010-EU6DR5570959050-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1366076
5°	1311827
10°	1306881
15°	1269343
20°	1138137
25°	940613
30°	710515
35°	515178
40°	329703
45°	150578
50°	49243
55°	21259
60°	9134
65°	1189
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 150578 cd/sqm



TEST NUMBER: P774630

CATALOG NUMBER: LD6D95BD010-EU6DR5570959050-6LBPD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1138.1	10.2
10°-20°	3106.2	27.9
20°-30°	3539.7	31.7
30°-40°	2409.7	21.6
40°-50°	830.4	7.4
50°-60°	114.8	1.0
60°-70°	11.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7784.0	69.8
0°-40°	10193.7	91.4
0°-60°	11138.9	99.9
0°-90°	11150.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11150.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12503	
5°	11961	###
15°	11222	3106
25°	7802	3540
35°	3862	2410
45°	974	830
55°	112	115
65°	5	11
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774630

CATALOG NUMBER: LD6D95BD010-EU6DR5570959050-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	12502.9
2.5°	12216.3
5°	11960.7
7.5°	11835.2
10°	11779.4
12.5°	11593.5
15°	11221.7
17.5°	10631.4
20°	9788.5
22.5°	8815.6
25°	7802.3
27.5°	6747.2
30°	5631.7
32.5°	4686.7
35°	3862.4
37.5°	3078.5
40°	2311.6
42.5°	1602.0
45°	974.5
47.5°	525.2
50°	289.7
52.5°	172.0
55°	111.6
57.5°	71.3
60°	41.8
62.5°	18.6
65°	4.6
67.5°	1.5
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)