

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204065

Luminaire Tested: **LD6B20D010 EU6B10209027 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204065
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209027 6LBNMW1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1208.0 lumens
Efficiency: N/A
Efficacy: 58.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204065

CATALOG NUMBER: LD6B20D010 EU6B10209027 6LBNMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204065

CATALOG NUMBER: LD6B20D010 EU6B10209027 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	108	105	103	109	106	103	101		102	100	98		98	97	95		95	93	92
2	105	99	94	90	102	97	92	89		94	90	87		91	87	85		88	85	83
3	98	90	84	79	96	89	83	79		86	81	77		84	80	76		81	78	75
4	92	83	76	71	90	82	76	71		80	74	70		77	73	69		75	71	68
5	87	77	70	64	85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	59	80	70	63	59		68	63	58		67	62	58		66	61	57
7	77	66	59	54	75	65	59	54		64	58	54		63	57	53		61	57	53
8	72	61	55	50	71	61	54	50		60	54	49		59	53	49		58	53	49
9	69	58	51	46	67	57	51	46		56	50	46		55	50	46		54	49	46
10	65	54	47	43	64	54	47	43		53	47	43		52	46	43		51	46	43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204065

CATALOG NUMBER: LD6B20D010 EU6B10209027 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	7.6
10°-20°	243.8	20.2
20°-30°	325.5	26.9
30°-40°	262.6	21.7
40°-50°	125.9	10.4
50°-60°	74.6	6.2
60°-70°	49.6	4.1
70°-80°	26.6	2.2
80°-90°	7.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	661.4	54.7
0°-40°	924.0	76.5
0°-60°	1124.5	93.1
0°-90°	1208.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1208.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	991	
5°	979	92
15°	868	244
25°	712	326
35°	420	263
45°	156	126
55°	83	75
65°	50	50
75°	25	27
85°	6	7
90°	0	



TEST NUMBER: P204065

CATALOG NUMBER: LD6B20D010 EU6B10209027 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	990.6
2.5°	990.6
5°	979.1
7.5°	959.9
10°	933.1
12.5°	904.3
15°	867.8
17.5°	833.2
20°	794.8
22.5°	754.5
25°	712.3
27.5°	668.1
30°	604.8
32.5°	516.4
35°	420.4
37.5°	332.1
40°	257.3
42.5°	199.7
45°	155.5
47.5°	122.9
50°	103.7
52.5°	92.2
55°	82.6
57.5°	74.9
60°	65.3
62.5°	57.6
65°	49.9
67.5°	42.2
70°	36.5
72.5°	30.7
75°	25.0
77.5°	19.2
80°	15.4
82.5°	11.5
85°	5.8
87.5°	1.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)