

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774711

Luminaire Tested: LD6D95BD010-EU6DR6070959050-6LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774711
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR6070959050-6LBS1LI
Description: 6 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13202.0 lumens
Efficiency: N/A
Efficacy: 133.1 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight

TEST NUMBER: P774711

CATALOG NUMBER: LD6D95BD010-EU6DR6070959050-6LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P774711

CATALOG NUMBER: LD6D95BD010-EU6DR6070959050-6LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1443531
5°	1439997
10°	1487834
15°	1489363
20°	1370380
25°	1165595
30°	888153
35°	628059
40°	368812
45°	148816
50°	49685
55°	23907
60°	9833
65°	1448
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 148816 cd/sqm

TEST NUMBER: P774711

CATALOG NUMBER: LD6D95BD010-EU6DR6070959050-6LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1266.5	9.6
10°-20°	3647.7	27.6
20°-30°	4365.8	33.1
30°-40°	2920.0	22.1
40°-50°	865.7	6.6
50°-60°	124.5	0.9
60°-70°	11.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9280.0	70.3
0°-40°	12200.0	92.4
0°-60°	13190.2	99.9
0°-90°	13202.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	13202.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13212	
5°	13129	###
15°	13167	3648
25°	9668	4366
35°	4709	2920
45°	963	866
55°	126	124
65°	6	12
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774711

CATALOG NUMBER: LD6D95BD010-EU6DR6070959050-6LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	13211.8
2.5°	13194.9
5°	13129.3
7.5°	13307.3
10°	13410.4
12.5°	13391.7
15°	13166.8
17.5°	12636.5
20°	11785.9
22.5°	10764.7
25°	9668.5
27.5°	8433.7
30°	7039.7
32.5°	5795.5
35°	4708.7
37.5°	3620.1
40°	2585.8
42.5°	1705.1
45°	963.1
47.5°	492.8
50°	292.3
52.5°	189.2
55°	125.5
57.5°	80.6
60°	45.0
62.5°	18.7
65°	5.6
67.5°	1.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)