

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204690

Luminaire Tested: **LD6B20D010 EU6B10209727 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204690
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209727 6LBPSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1633.7 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204690

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBPSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204690

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63		
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47		
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37		
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33		
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30		
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204690

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.4	3.8
10°-20°	177.8	10.9
20°-30°	267.7	16.4
30°-40°	318.6	19.5
40°-50°	318.0	19.5
50°-60°	258.6	15.8
60°-70°	159.1	9.7
70°-80°	61.6	3.8
80°-90°	9.9	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	507.9	31.1
0°-40°	826.5	50.6
0°-60°	1403.1	85.9
0°-90°	1633.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1633.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	658	
5°	656	62
15°	631	178
25°	583	268
35°	510	319
45°	413	318
55°	289	259
65°	160	159
75°	56	62
85°	8	10
90°	0	



TEST NUMBER: P204690

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	658.2
2.5°	659.2
5°	656.3
7.5°	652.4
10°	647.6
12.5°	638.9
15°	631.1
17.5°	619.5
20°	606.9
22.5°	595.3
25°	582.7
27.5°	565.3
30°	547.9
32.5°	531.4
35°	510.1
37.5°	486.9
40°	465.6
42.5°	439.5
45°	413.3
47.5°	385.2
50°	355.2
52.5°	324.3
55°	289.4
57.5°	255.5
60°	222.6
62.5°	190.7
65°	159.7
67.5°	130.7
70°	103.6
72.5°	78.4
75°	56.1
77.5°	36.8
80°	22.3
82.5°	13.6
85°	7.7
87.5°	3.9
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)