

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204276

Luminaire Tested: **LD6B20D010 EU6B10209727 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209727 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1524.3 lumens
Efficiency: N/A
Efficacy: 73.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204276

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204276

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89		
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77		
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67		
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59		
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47		
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204276

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.8	5.5
10°-20°	217.0	14.2
20°-30°	283.9	18.6
30°-40°	300.6	19.7
40°-50°	280.3	18.4
50°-60°	212.3	13.9
60°-70°	115.0	7.5
70°-80°	30.9	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	584.7	38.4
0°-40°	885.3	58.1
0°-60°	1378.0	90.4
0°-90°	1524.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1524.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	909	
5°	896	84
15°	776	217
25°	617	284
35°	480	301
45°	365	280
55°	238	212
65°	115	115
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P204276

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	909.1
2.5°	905.7
5°	895.7
7.5°	874.1
10°	845.7
12.5°	812.3
15°	775.6
17.5°	733.9
20°	697.2
22.5°	655.5
25°	617.2
27.5°	578.8
30°	542.1
32.5°	510.4
35°	480.4
37.5°	450.4
40°	422.0
42.5°	393.7
45°	365.3
47.5°	333.6
50°	301.9
52.5°	270.2
55°	238.5
57.5°	205.2
60°	173.5
62.5°	143.5
65°	115.1
67.5°	88.4
70°	65.1
72.5°	45.0
75°	26.7
77.5°	11.7
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)