

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203341

Luminaire Tested: **LD6B20D010 EU6B10208040 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203341
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208040 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1666.4 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203341

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203341

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	78	70	64	60	69	64	60		68	63	60		67
9	76	66	61	57	75	66	60	57	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203341

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	190.0	11.4
10°-20°	466.6	28.0
20°-30°	539.8	32.4
30°-40°	345.1	20.7
40°-50°	97.8	5.9
50°-60°	17.5	1.0
60°-70°	7.1	0.4
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1196.4	71.8
0°-40°	1541.5	92.5
0°-60°	1656.8	99.4
0°-90°	1666.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1666.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2079	
5°	2042	190
15°	1673	467
25°	1191	540
35°	545	345
45°	114	98
55°	16	17
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203341

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2078.8
2.5°	2076.5
5°	2041.7
7.5°	1979.2
10°	1891.1
12.5°	1789.1
15°	1673.3
17.5°	1552.7
20°	1434.5
22.5°	1318.7
25°	1191.2
27.5°	1052.2
30°	896.9
32.5°	723.1
35°	544.6
37.5°	394.0
40°	273.5
42.5°	180.8
45°	113.6
47.5°	67.2
50°	39.4
52.5°	23.2
55°	16.2
57.5°	13.9
60°	11.6
62.5°	9.3
65°	7.0
67.5°	4.6
70°	4.6
72.5°	2.3
75°	2.3
77.5°	2.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)