

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203650

Luminaire Tested: **LD6B20D010 EU6B10208040 6LBNH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208040 6LBNH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1327.8 lumens
Efficiency: N/A
Efficacy: 63.8 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203650

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBNH1

Luminous Intensity Polar Plot





TEST NUMBER: P203650

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBNH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106	111	109	106	104		104	103	101			101	99	98			97
2	108	103	99	96	106	101	98	94		98	95	92			95	93	90			92
3	102	96	91	87	100	95	90	86		92	88	85			90	86	84			87
4	97	90	84	80	95	89	83	79		86	82	78			84	81	78			83
5	92	84	78	74	91	83	78	73		81	76	73			80	75	72			78
6	88	79	73	69	86	78	72	68		77	72	68			75	71	67			74
7	83	74	68	64	82	73	68	64		72	67	63			71	66	63			70
8	79	70	64	60	78	69	64	60		68	63	59			67	63	59			66
9	76	66	60	56	75	66	60	56		65	59	56			64	59	56			63
10	72	62	57	53	71	62	57	53		61	56	53			60	56	52			60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203650

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBNH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.1	11.5
10°-20°	365.0	27.5
20°-30°	418.2	31.5
30°-40°	281.0	21.2
40°-50°	80.3	6.0
50°-60°	19.6	1.5
60°-70°	7.5	0.6
70°-80°	2.9	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.2	70.5
0°-40°	1217.2	91.7
0°-60°	1317.1	99.2
0°-90°	1327.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1327.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1702	
5°	1654	153
15°	1310	365
25°	913	418
35°	448	281
45°	92	80
55°	22	20
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P203650

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBNH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1702.1
2.5°	1690.0
5°	1653.6
7.5°	1588.3
10°	1508.4
12.5°	1406.7
15°	1309.8
17.5°	1208.2
20°	1106.5
22.5°	1009.6
25°	912.8
27.5°	823.2
30°	719.1
32.5°	581.1
35°	447.9
37.5°	326.9
40°	225.2
42.5°	147.7
45°	92.0
47.5°	55.7
50°	33.9
52.5°	26.6
55°	21.8
57.5°	16.9
60°	12.1
62.5°	9.7
65°	7.3
67.5°	4.8
70°	4.8
72.5°	2.4
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)