

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P760774

Luminaire Tested: LD6D10D010-EU6DR650210IC9050-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P760774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D10D010-EU6DR650210IC9050-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 998.8 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P760774

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9050-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P760774

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9050-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93						
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85						
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78						
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72						
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66						
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61						
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56						
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52						
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49						
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	52966
5°	52829
10°	52787
15°	51159
20°	46577
25°	40585
30°	33753
35°	26751
40°	19304
45°	12191
50°	6360
55°	3381
60°	1775
65°	967
70°	410
75°	451
80°	303
85°	268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12191 cd/sqm



TEST NUMBER: P760774

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9050-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	8.6
10°-20°	234.9	23.5
20°-30°	287.1	28.7
30°-40°	232.9	23.3
40°-50°	116.1	11.6
50°-60°	32.4	3.2
60°-70°	7.3	0.7
70°-80°	1.9	0.2
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.7	60.8
0°-40°	840.6	84.2
0°-60°	989.0	99.0
0°-90°	998.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	998.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	907	
5°	901	86
15°	846	235
25°	630	287
35°	375	233
45°	148	116
55°	33	32
65°	7	7
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P760774

CATALOG NUMBER: LD6D10D010-EU6DR650210IC9050-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	906.9
2.5°	906.2
5°	901.1
7.5°	898.2
10°	890.1
12.5°	873.6
15°	846.1
17.5°	803.2
20°	749.4
22.5°	691.3
25°	629.8
27.5°	564.1
30°	500.5
32.5°	437.8
35°	375.2
37.5°	312.7
40°	253.2
42.5°	197.5
45°	147.6
47.5°	102.9
50°	70.0
52.5°	48.2
55°	33.2
57.5°	22.4
60°	15.2
62.5°	10.5
65°	7.0
67.5°	3.6
70°	2.4
72.5°	2.3
75°	2.0
77.5°	1.3
80°	0.9
82.5°	0.7
85°	0.4
87.5°	0.3
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)