

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204894

Luminaire Tested: **LD6B20D010 EU6B10209040 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204894
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209040 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1640.9 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204894

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBCSMB1

Luminous Intensity Polar Plot






TEST NUMBER: P204894

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88		
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75		
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65		
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56		
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49		
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43		
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39		
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35		
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31		
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204894

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.5	4.0
10°-20°	186.7	11.4
20°-30°	280.7	17.1
30°-40°	333.0	20.3
40°-50°	329.6	20.1
50°-60°	258.8	15.8
60°-70°	145.1	8.8
70°-80°	40.7	2.5
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.9	32.5
0°-40°	865.9	52.8
0°-60°	1454.3	88.6
0°-90°	1640.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1640.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	693	
5°	692	66
15°	662	187
25°	609	281
35°	534	333
45°	429	330
55°	292	259
65°	145	145
75°	35	41
85°	0	1
90°	0	



TEST NUMBER: P204894

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

0°	
0°	692.9
2.5°	690.5
5°	691.7
7.5°	685.8
10°	678.7
12.5°	670.5
15°	662.3
17.5°	651.7
20°	637.6
22.5°	623.5
25°	609.3
27.5°	594.1
30°	574.1
32.5°	554.1
35°	534.1
37.5°	510.5
40°	483.5
42.5°	457.6
45°	429.4
47.5°	397.6
50°	364.7
52.5°	327.0
55°	291.7
57.5°	251.7
60°	214.1
62.5°	180.0
65°	144.7
67.5°	114.1
70°	84.7
72.5°	57.6
75°	35.3
77.5°	17.6
80°	4.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)