

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P736029

Luminaire Tested: LD6D15D010-EU6DR250215IC9035-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P736029
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D15D010-EU6DR250215IC9035-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 25° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1227.6 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.42 / 0.42 / 0.45
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P736029

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9035-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P736029

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9035-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	113	111	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		97
3	107	102	98	95	105	101	97	94	98	95	93		96	93	91		94
4	103	97	93	90	102	96	93	90	94	91	89		93	90	88		91
5	100	93	89	86	98	93	89	86	91	87	85		89	86	84		88
6	97	90	85	82	95	89	85	82	88	84	81		87	83	81		85
7	93	87	82	79	92	86	82	79	85	81	78		84	80	78		83
8	91	84	79	76	90	83	79	76	82	78	76		81	78	75		80
9	88	81	76	73	87	80	76	73	80	76	73		79	75	73		78
10	85	78	74	71	85	78	74	71	77	73	71		76	73	71		76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	200471
5°	186711
10°	133188
15°	78442
20°	48806
25°	26784
30°	12250
35°	4641
40°	2102
45°	1260
50°	522
55°	338
60°	241
65°	153
70°	25
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1260 cd/sqm



TEST NUMBER: P736029

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9035-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	371.3	30.2
10°-20°	502.9	41.0
20°-30°	266.1	21.7
30°-40°	65.7	5.4
40°-50°	16.0	1.3
50°-60°	4.2	0.3
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1140.2	92.9
0°-40°	1205.9	98.2
0°-60°	1226.2	99.9
0°-90°	1227.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1227.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4656	
5°	4320	371
15°	1760	503
25°	564	266
35°	88	66
45°	21	16
55°	4	4
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P736029

CATALOG NUMBER: LD6D15D010-EU6DR250215IC9035-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4656.1
2.5°	4579.5
5°	4320.0
7.5°	3798.7
10°	3046.4
12.5°	2302.9
15°	1759.8
17.5°	1371.5
20°	1065.2
22.5°	798.9
25°	563.8
27.5°	378.1
30°	246.4
32.5°	149.9
35°	88.3
37.5°	54.0
40°	37.4
42.5°	28.6
45°	20.7
47.5°	12.5
50°	7.8
52.5°	5.7
55°	4.5
57.5°	3.5
60°	2.8
62.5°	2.2
65°	1.5
67.5°	0.6
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)