

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203862

Luminaire Tested: **LD6B20D010 EU6B10209040 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209040 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 889.3 lumens
Efficiency: N/A
Efficacy: 42.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203862

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203862

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	79	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203862

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.8	11.0
10°-20°	241.3	27.1
20°-30°	292.4	32.9
30°-40°	199.3	22.4
40°-50°	47.5	5.3
50°-60°	7.4	0.8
60°-70°	2.7	0.3
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	631.6	71.0
0°-40°	830.8	93.4
0°-60°	885.7	99.6
0°-90°	889.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	889.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1081	
5°	1050	98
15°	864	241
25°	639	292
35°	318	199
45°	51	47
55°	8	7
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203862

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1080.9
2.5°	1074.8
5°	1050.5
7.5°	1018.1
10°	971.4
12.5°	918.7
15°	863.9
17.5°	807.1
20°	750.4
22.5°	693.6
25°	638.8
27.5°	588.1
30°	515.1
32.5°	419.8
35°	318.4
37.5°	227.1
40°	150.1
42.5°	93.3
45°	50.7
47.5°	26.4
50°	14.2
52.5°	10.1
55°	8.1
57.5°	6.1
60°	4.1
62.5°	4.1
65°	2.0
67.5°	2.0
70°	2.0
72.5°	2.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)