

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P757547

Luminaire Tested: LD6D02D010-EU6DR550210IC9030-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P757547
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D02D010-EU6DR550210IC9030-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 337.8 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P757547

CATALOG NUMBER: LD6D02D010-EU6DR550210IC9030-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P757547

CATALOG NUMBER: LD6D02D010-EU6DR550210IC9030-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94						
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87						
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81						
4	97	90	84	80	95	88	83	79	86	82	78	84	81	77	82	79	77	75						
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70						
6	88	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65						
7	83	74	68	64	82	73	67	63	72	67	63	71	66	63	70	65	62	61						
8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	62	58	57						
9	75	66	60	56	74	65	59	55	64	59	55	63	58	55	62	58	55	54						
10	72	62	56	52	71	61	56	52	61	56	52	60	55	52	59	55	52	50						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41377
5°	39736
10°	39586
15°	38448
20°	34475
25°	28487
30°	21523
35°	15606
40°	9984
45°	4558
50°	1496
55°	648
60°	284
65°	26
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4558 cd/sqm



TEST NUMBER: P757547

CATALOG NUMBER: LD6D02D010-EU6DR550210IC9030-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.5	10.2
10°-20°	94.1	27.9
20°-30°	107.2	31.7
30°-40°	73.0	21.6
40°-50°	25.1	7.4
50°-60°	3.5	1.0
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	235.8	69.8
0°-40°	308.8	91.4
0°-60°	337.4	99.9
0°-90°	337.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	337.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	379	
5°	362	34
15°	340	94
25°	236	107
35°	117	73
45°	30	25
55°	3	3
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P757547

CATALOG NUMBER: LD6D02D010-EU6DR550210IC9030-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	378.7
2.5°	370.0
5°	362.3
7.5°	358.5
10°	356.8
12.5°	351.2
15°	339.9
17.5°	322.0
20°	296.5
22.5°	267.0
25°	236.3
27.5°	204.4
30°	170.6
32.5°	142.0
35°	117.0
37.5°	93.2
40°	70.0
42.5°	48.5
45°	29.5
47.5°	15.9
50°	8.8
52.5°	5.2
55°	3.4
57.5°	2.2
60°	1.3
62.5°	0.6
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)