

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768344

Luminaire Tested: LD6D55D010-EU6DR5555659027-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR5555659027-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5888.8 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768344

CATALOG NUMBER: LD6D55D010-EU6DR5555659027-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P768344

CATALOG NUMBER: LD6D55D010-EU6DR5555659027-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	721492
5°	692837
10°	690230
15°	670399
20°	601107
25°	496787
30°	375261
35°	272087
40°	174122
45°	79530
50°	26007
55°	11220
60°	4829
65°	646
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 79530 cd/sqm



TEST NUMBER: P768344

CATALOG NUMBER: LD6D55D010-EU6DR5555659027-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	601.1	10.2
10°-20°	1640.5	27.9
20°-30°	1869.5	31.7
30°-40°	1272.7	21.6
40°-50°	438.6	7.4
50°-60°	60.6	1.0
60°-70°	5.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4111.1	69.8
0°-40°	5383.8	91.4
0°-60°	5882.9	99.9
0°-90°	5888.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5888.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6603	
5°	6317	601
15°	5927	1641
25°	4121	1870
35°	2040	1273
45°	515	439
55°	59	61
65°	2	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768344

CATALOG NUMBER: LD6D55D010-EU6DR5555659027-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	6603.4
2.5°	6452.0
5°	6317.0
7.5°	6250.7
10°	6221.3
12.5°	6123.1
15°	5926.7
17.5°	5614.9
20°	5169.8
22.5°	4655.9
25°	4120.8
27.5°	3563.5
30°	2974.4
32.5°	2475.2
35°	2039.9
37.5°	1625.9
40°	1220.8
42.5°	846.1
45°	514.7
47.5°	277.4
50°	153.0
52.5°	90.8
55°	58.9
57.5°	37.6
60°	22.1
62.5°	9.8
65°	2.5
67.5°	0.8
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)