

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768423

Luminaire Tested: LD6D55D010-EU6DR6055659030-6LBCSSQMB

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768423
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR6055659030-6LBCSSQMB
Description: 6 INCH SQAURE SHALLOW CAST MATTE BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6362.9 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768423

CATALOG NUMBER: LD6D55D010-EU6DR6055659030-6LBCSSQMB

Luminous Intensity Polar Plot





TEST NUMBER: P768423

CATALOG NUMBER: LD6D55D010-EU6DR6055659030-6LBCSSQMB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	87	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	63	82	73	67	63	72	67	63		71	66	63		69
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	695729
5°	694032
10°	717079
15°	717817
20°	660465
25°	561778
30°	428060
35°	302699
40°	177745
45°	71727
50°	23950
55°	11525
60°	4742
65°	698
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 71727 cd/sqm

TEST NUMBER: P768423

CATALOG NUMBER: LD6D55D010-EU6DR6055659030-6LBCSSQMB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	610.4	9.6
10°-20°	1758.0	27.6
20°-30°	2104.2	33.1
30°-40°	1407.3	22.1
40°-50°	417.3	6.6
50°-60°	60.0	0.9
60°-70°	5.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4472.6	70.3
0°-40°	5879.9	92.4
0°-60°	6357.2	99.9
0°-90°	6362.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6362.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6368	
5°	6328	610
15°	6346	1758
25°	4660	2104
35°	2269	1407
45°	464	417
55°	60	60
65°	3	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768423

CATALOG NUMBER: LD6D55D010-EU6DR6055659030-6LBCSSQMB

CANDELA DISTRIBUTION (FULL):

	0°
0°	6367.6
2.5°	6359.5
5°	6327.9
7.5°	6413.6
10°	6463.3
12.5°	6454.3
15°	6345.9
17.5°	6090.3
20°	5680.3
22.5°	5188.2
25°	4659.9
27.5°	4064.7
30°	3392.9
32.5°	2793.2
35°	2269.4
37.5°	1744.7
40°	1246.2
42.5°	821.8
45°	464.2
47.5°	237.5
50°	140.9
52.5°	91.2
55°	60.5
57.5°	38.8
60°	21.7
62.5°	9.0
65°	2.7
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)