

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P768360

Luminaire Tested: LD6D55D010-EU6DR5555659035-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P768360
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D55D010-EU6DR5555659035-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 55° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6658.1 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.87
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 58.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P768360

CATALOG NUMBER: LD6D55D010-EU6DR5555659035-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P768360

CATALOG NUMBER: LD6D55D010-EU6DR5555659035-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	70	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	815741
5°	783343
10°	780385
15°	757973
20°	679627
25°	561682
30°	424275
35°	307634
40°	196872
45°	89914
50°	29406
55°	12687
60°	5463
65°	724
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 89914 cd/sqm

TEST NUMBER: P768360

CATALOG NUMBER: LD6D55D010-EU6DR5555659035-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	679.6	10.2
10°-20°	1854.8	27.9
20°-30°	2113.7	31.7
30°-40°	1438.9	21.6
40°-50°	495.8	7.4
50°-60°	68.6	1.0
60°-70°	6.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4648.1	69.8
0°-40°	6087.1	91.4
0°-60°	6651.4	99.9
0°-90°	6658.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6658.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7466	
5°	7142	680
15°	6701	1855
25°	4659	2114
35°	2306	1439
45°	582	496
55°	67	69
65°	3	7
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P768360

CATALOG NUMBER: LD6D55D010-EU6DR5555659035-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7466.0
2.5°	7294.8
5°	7142.2
7.5°	7067.2
10°	7033.9
12.5°	6922.9
15°	6700.9
17.5°	6348.4
20°	5845.1
22.5°	5264.1
25°	4659.1
27.5°	4029.0
30°	3362.9
32.5°	2798.6
35°	2306.4
37.5°	1838.3
40°	1380.3
42.5°	956.6
45°	581.9
47.5°	313.6
50°	173.0
52.5°	102.7
55°	66.6
57.5°	42.6
60°	25.0
62.5°	11.1
65°	2.8
67.5°	0.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)