

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P769699

Luminaire Tested: LD6D65D010-EU6DR4055659040-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P769699
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-28)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D65D010-EU6DR4055659040-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 40° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8278.5 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.6
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P769699

CATALOG NUMBER: LD6D65D010-EU6DR4055659040-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P769699

CATALOG NUMBER: LD6D65D010-EU6DR4055659040-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	97	96						
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92						
3	106	101	97	94	104	100	96	93	97	94	92	95	93	90	93	91	89	88						
4	102	97	92	89	101	95	91	88	93	90	87	92	89	86	90	87	85	84						
5	99	92	88	84	97	91	87	84	90	86	83	88	85	83	87	84	82	81						
6	95	88	84	80	94	88	83	80	86	82	80	85	82	79	84	81	79	77						
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	74						
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72						
9	86	79	74	71	85	78	74	71	77	73	71	76	73	70	76	72	70	69						
10	83	76	71	68	82	75	71	68	75	71	68	74	70	68	73	70	68	67						

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2105935
5°	2095707
10°	1980901
15°	1684012
20°	1147776
25°	478896
30°	150576
35°	69986
40°	38710
45°	17739
50°	8618
55°	4724
60°	2469
65°	879
70°	351
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17739 cd/sqm



TEST NUMBER: P769699

CATALOG NUMBER: LD6D65D010-EU6DR4055659040-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1784.2	21.6
10°-20°	3997.1	48.3
20°-30°	2000.8	24.2
30°-40°	366.8	4.4
40°-50°	101.2	1.2
50°-60°	23.8	0.3
60°-70°	4.6	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7782.0	94.0
0°-40°	8148.8	98.4
0°-60°	8273.8	99.9
0°-90°	8278.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8278.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	19274	
5°	19108	###
15°	14888	3997
25°	3972	2001
35°	525	367
45°	115	101
55°	25	24
65°	3	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P769699

CATALOG NUMBER: LD6D65D010-EU6DR4055659040-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	19274.4
2.5°	19246.3
5°	19107.8
7.5°	18666.4
10°	17854.6
12.5°	16589.0
15°	14887.6
17.5°	12675.1
20°	9871.4
22.5°	6729.9
25°	3972.4
27.5°	2099.9
30°	1193.5
32.5°	771.3
35°	524.7
37.5°	374.9
40°	271.4
42.5°	185.8
45°	114.8
47.5°	73.2
50°	50.7
52.5°	36.0
55°	24.8
57.5°	15.8
60°	11.3
62.5°	6.8
65°	3.4
67.5°	2.3
70°	1.1
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)