

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204588

Luminaire Tested: **LD6B30D010 EU6B30508027 6LBSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204588
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508027 6LBSMW1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3070.1 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204588

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204588

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86		
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74		
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63		
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54		
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47		
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42		
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37		
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33		
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30		
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204588

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.2	3.8
10°-20°	334.1	10.9
20°-30°	503.1	16.4
30°-40°	598.7	19.5
40°-50°	597.6	19.5
50°-60°	486.0	15.8
60°-70°	299.0	9.7
70°-80°	115.8	3.8
80°-90°	18.6	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	954.4	31.1
0°-40°	1553.1	50.6
0°-60°	2636.8	85.9
0°-90°	3070.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3070.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1237	
5°	1233	117
15°	1186	334
25°	1095	503
35°	959	599
45°	777	598
55°	544	486
65°	300	299
75°	106	116
85°	15	19
90°	0	



TEST NUMBER: P204588

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1237.0
2.5°	1238.8
5°	1233.3
7.5°	1226.0
10°	1217.0
12.5°	1200.6
15°	1186.0
17.5°	1164.2
20°	1140.6
22.5°	1118.7
25°	1095.1
27.5°	1062.3
30°	1029.6
32.5°	998.7
35°	958.6
37.5°	915.0
40°	875.0
42.5°	825.9
45°	776.7
47.5°	724.0
50°	667.6
52.5°	609.4
55°	543.9
57.5°	480.2
60°	418.4
62.5°	358.4
65°	300.1
67.5°	245.6
70°	194.6
72.5°	147.3
75°	105.5
77.5°	69.1
80°	41.8
82.5°	25.5
85°	14.6
87.5°	7.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)