

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203042

Luminaire Tested: **LD6B30D010 EU6B30508027 6LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203042
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508027 6LBWB1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1590.1 lumens
Efficiency: N/A
Efficacy: 56.8 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203042

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBWB1

Luminous Intensity Polar Plot





TEST NUMBER: P203042

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	73		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	83	73	67	62	82	72	66	61	71	65	61		69	64	61		68
7	78	68	61	56	77	67	61	56	66	60	56		65	60	56		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203042

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.7	7.1
10°-20°	315.1	19.8
20°-30°	441.4	27.8
30°-40°	421.5	26.5
40°-50°	240.1	15.1
50°-60°	58.6	3.7
60°-70°	0.8	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	869.1	54.7
0°-40°	1290.7	81.2
0°-60°	1589.3	100.0
0°-90°	1590.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1590.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1198	
5°	1189	113
15°	1118	315
25°	965	441
35°	687	422
45°	308	240
55°	58	59
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203042

CATALOG NUMBER: LD6B30D010 EU6B30508027 6LBWB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1198.4
2.5°	1198.4
5°	1188.7
7.5°	1175.8
10°	1166.0
12.5°	1146.6
15°	1117.5
17.5°	1091.5
20°	1059.2
22.5°	1017.1
25°	965.2
27.5°	906.9
30°	842.1
32.5°	764.4
35°	686.7
37.5°	592.7
40°	492.3
42.5°	398.4
45°	307.7
47.5°	226.7
50°	158.7
52.5°	100.4
55°	58.3
57.5°	25.9
60°	6.5
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)