

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202636

Luminaire Tested: **LD6B30D010 EU6B30509027 6LBMWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202636
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509027 6LBMWMH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1904.2 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.89
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202636

CATALOG NUMBER: LD6B30D010 EU6B30509027 6LBMWMH1

Luminous Intensity Polar Plot





TEST NUMBER: P202636

CATALOG NUMBER: LD6B30D010 EU6B30509027 6LBMWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	113	111	108	106		111	108	106	104		104	103	101			101	99	98			93
2	108	103	99	95		105	101	97	94		98	95	92			95	92	90			86
3	102	95	90	86		100	94	89	86		91	88	84			89	86	83			80
4	97	89	83	79		95	88	83	79		86	81	78			84	80	77			74
5	92	83	77	73		90	82	77	73		80	76	72			79	75	71			69
6	87	78	72	67		85	77	71	67		76	71	67			74	70	66			64
7	83	73	67	63		81	72	67	63		71	66	62			70	65	62			60
8	78	69	63	58		77	68	62	58		67	62	58			66	61	58			56
9	75	65	59	55		73	64	59	55		63	58	54			62	58	54			53
10	71	61	55	51		70	61	55	51		60	55	51			59	54	51			50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202636

CATALOG NUMBER: LD6B30D010 EU6B30509027 6LBMWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.4	10.2
10°-20°	498.9	26.2
20°-30°	612.8	32.2
30°-40°	420.2	22.1
40°-50°	135.1	7.1
50°-60°	27.4	1.4
60°-70°	10.8	0.6
70°-80°	4.0	0.2
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1306.1	68.6
0°-40°	1726.3	90.7
0°-60°	1888.8	99.2
0°-90°	1904.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1904.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2118	
5°	2077	194
15°	1785	499
25°	1352	613
35°	670	420
45°	160	135
55°	28	27
65°	11	11
75°	3	4
85°	0	1
90°	0	



TEST NUMBER: P202636

CATALOG NUMBER: LD6B30D010 EU6B30509027 6LBMWMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2117.6
2.5°	2104.7
5°	2077.2
7.5°	2025.5
10°	1956.1
12.5°	1870.5
15°	1784.9
17.5°	1689.6
20°	1584.6
22.5°	1474.7
25°	1352.0
27.5°	1216.3
30°	1045.1
32.5°	856.1
35°	670.3
37.5°	500.7
40°	360.2
42.5°	245.5
45°	159.9
47.5°	98.5
50°	59.8
52.5°	37.2
55°	27.5
57.5°	21.0
60°	16.2
62.5°	12.9
65°	11.3
67.5°	8.1
70°	6.5
72.5°	4.8
75°	3.2
77.5°	3.2
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)