

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P773248

Luminaire Tested: LD6D85BD010-EU6DR7070959027-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P773248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR7070959027-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10014.0 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.1 / 1.1 / 1.04
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P773248

CATALOG NUMBER: LD6D85BD010-EU6DR7070959027-6LBCSSQMW

Luminous Intensity Polar Plot





TEST NUMBER: P773248

CATALOG NUMBER: LD6D85BD010-EU6DR7070959027-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	92	97	93	90		94	91	88		91
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		85
4	95	87	81	76	93	86	80	76	83	78	75		81	77	74		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	84	75	68	63	83	74	68	63	72	67	63		71	66	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	58	54	74	64	58	54	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	53	50		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	863586
5°	861434
10°	859567
15°	859324
20°	850931
25°	799334
30°	712609
35°	568171
40°	377270
45°	225550
50°	116929
55°	61452
60°	21743
65°	362
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 225550 cd/sqm



TEST NUMBER: P773248

CATALOG NUMBER: LD6D85BD010-EU6DR7070959027-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	746.9	7.5
10°-20°	2142.2	21.4
20°-30°	3022.0	30.2
30°-40°	2608.8	26.1
40°-50°	1168.3	11.7
50°-60°	305.8	3.1
60°-70°	19.9	0.2
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5911.2	59.0
0°-40°	8520.0	85.1
0°-60°	9994.1	99.8
0°-90°	10014.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10014.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7904	
5°	7854	747
15°	7597	2142
25°	6630	3022
35°	4260	2609
45°	1460	1168
55°	323	306
65°	1	20
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P773248

CATALOG NUMBER: LD6D85BD010-EU6DR7070959027-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7903.9
2.5°	7895.4
5°	7854.2
7.5°	7820.1
10°	7747.6
12.5°	7682.2
15°	7596.9
17.5°	7498.9
20°	7318.4
22.5°	7021.3
25°	6630.4
27.5°	6177.0
30°	5648.3
32.5°	5001.6
35°	4259.7
37.5°	3441.0
40°	2645.1
42.5°	2009.7
45°	1459.7
47.5°	1006.3
50°	687.9
52.5°	474.7
55°	322.6
57.5°	194.7
60°	99.5
62.5°	31.3
65°	1.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)