

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P772751

Luminaire Tested: LD6D85BD010-EU6DR3570959040-6LBSQW1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P772751
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D85BD010-EU6DR3570959040-6LBSQW1MW
Description: 6 INCH SQAURE DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9513.3 lumens
Efficiency: N/A
Efficacy: 108.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 87.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P772751

CATALOG NUMBER: LD6D85BD010-EU6DR3570959040-6LBSQW1MW

Luminous Intensity Polar Plot





TEST NUMBER: P772751

CATALOG NUMBER: LD6D85BD010-EU6DR3570959040-6LBSQW1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	112	110	108		112	110	108	107		106	105	103		103	101	100		99	98	98
2	110	106	103	101		108	105	102	99		102	99	97		99	97	95		96	95	93
3	106	101	97	94		105	100	96	93		97	95	92		95	93	91		93	91	89
4	103	97	92	89		101	96	92	89		94	90	88		92	89	87		90	88	86
5	99	93	88	85		98	92	87	84		90	86	84		89	85	83		87	84	82
6	96	89	84	81		94	88	84	81		87	83	80		85	82	80		84	81	79
7	93	85	81	78		91	85	80	77		84	80	77		83	79	77		82	79	76
8	90	82	78	74		88	82	77	74		81	77	74		80	76	74		79	76	73
9	87	79	75	72		86	79	75	72		78	74	71		77	74	71		77	73	71
10	84	77	72	69		83	76	72	69		76	72	69		75	71	69		74	71	69

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2859988
5°	2792789
10°	2517038
15°	1953621
20°	1108069
25°	431084
30°	160821
35°	88153
40°	57622
45°	35076
50°	22318
55°	15773
60°	11538
65°	6282
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 35076 cd/sqm



TEST NUMBER: P772751

CATALOG NUMBER: LD6D85BD010-EU6DR3570959040-6LBSQW1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2341.9	24.6
10°-20°	4572.4	48.1
20°-30°	1864.8	19.6
30°-40°	446.2	4.7
40°-50°	186.0	2.0
50°-60°	77.0	0.8
60°-70°	24.1	0.3
70°-80°	0.5	0.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8779.0	92.3
0°-40°	9225.3	97.0
0°-60°	9488.2	99.7
0°-90°	9513.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9513.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	26176	
5°	25464	###
15°	17271	4572
25°	3576	1865
35°	661	446
45°	227	186
55°	83	77
65°	24	24
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P772751

CATALOG NUMBER: LD6D85BD010-EU6DR3570959040-6LBSQW1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	26175.8
2.5°	26018.8
5°	25463.5
7.5°	24355.7
10°	22687.0
12.5°	20337.4
15°	17271.1
17.5°	13521.1
20°	9529.9
22.5°	6076.8
25°	3575.8
27.5°	2021.3
30°	1274.7
32.5°	895.0
35°	660.9
37.5°	511.0
40°	404.0
42.5°	311.2
45°	227.0
47.5°	169.9
50°	131.3
52.5°	104.2
55°	82.8
57.5°	67.1
60°	52.8
62.5°	38.5
65°	24.3
67.5°	8.6
70°	1.4
72.5°	1.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°







(END OF REPORT)