

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P774483

Luminaire Tested: LD6D95BD010-EU6DR5070959024-6LBCSSQMW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P774483
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD6D95BD010-EU6DR5070959024-6LBCSSQMW
Description: 6 INCH SQAURE SHALLOW CAST MATTE WHITE TRIM, WITH 50° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9646.1 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.73
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 99.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P774483

CATALOG NUMBER: LD6D95BD010-EU6DR5070959024-6LBCSSQMW

Luminous Intensity Polar Plot



TEST NUMBER: P774483

CATALOG NUMBER: LD6D95BD010-EU6DR5070959024-6LBCSSQMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107	112	110	108	106		106	104	102		102	101	99		98	97	97
2	109	105	101	98	107	103	100	97		100	98	95		97	95	93		95	93	91
3	105	99	95	91	103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85	99	93	88	85		90	87	84		89	85	83		87	84	82
5	96	89	84	80	95	88	83	79		86	82	79		85	81	78		83	80	77
6	92	84	79	75	91	83	79	75		82	78	74		81	77	74		79	76	74
7	88	80	75	71	87	79	74	71		78	74	71		77	73	70		76	73	70
8	85	76	71	67	84	76	71	67		75	70	67		74	70	67		73	69	66
9	81	73	68	64	80	72	67	64		71	67	64		71	67	64		70	66	63
10	78	70	64	61	77	69	64	61		68	64	61		68	64	61		67	63	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1698163
5°	1680367
10°	1652689
15°	1504905
20°	1252247
25°	888919
30°	470501
35°	191738
40°	71215
45°	32603
50°	13360
55°	6991
60°	3431
65°	1008
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 32603 cd/sqm



TEST NUMBER: P774483

CATALOG NUMBER: LD6D95BD010-EU6DR5070959024-6LBCSSQMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1448.1	15.0
10°-20°	3659.7	37.9
20°-30°	3287.4	34.1
30°-40°	1029.3	10.7
40°-50°	180.2	1.9
50°-60°	35.9	0.4
60°-70°	5.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8395.3	87.0
0°-40°	9424.5	97.7
0°-60°	9640.7	99.9
0°-90°	9646.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9646.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15542	
5°	15321	###
15°	13304	3660
25°	7374	3287
35°	1438	1029
45°	211	180
55°	37	36
65°	4	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P774483

CATALOG NUMBER: LD6D95BD010-EU6DR5070959024-6LBCSSQMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	15542.3
2.5°	15465.0
5°	15320.9
7.5°	15100.7
10°	14896.3
12.5°	14241.1
15°	13304.2
17.5°	12114.4
20°	10769.9
22.5°	9214.5
25°	7373.5
27.5°	5421.0
30°	3729.3
32.5°	2428.1
35°	1437.5
37.5°	825.5
40°	499.3
42.5°	325.0
45°	211.0
47.5°	128.4
50°	78.6
52.5°	53.7
55°	36.7
57.5°	24.9
60°	15.7
62.5°	9.2
65°	3.9
67.5°	1.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-T8S5UU9





— 0°-180°







(END OF REPORT)