

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203755

Luminaire Tested: **LD6B20D010 EU6B10209024 6LBNWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203755  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B20D010 EU6B10209024 6LBNWH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 992.0 lumens  
Efficiency: N/A  
Efficacy: 47.7 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.64  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203755

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBNWH1

### Luminous Intensity Polar Plot






TEST NUMBER: P203755

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBNWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 |  | 101 | 100 | 99  |  | 98  |
| 2   | 109 | 104 | 101 | 97  | 107 | 103 | 99  | 96  | 99  | 97  | 94  |  | 96  | 94  | 92  |  | 94  |
| 3   | 104 | 98  | 93  | 90  | 102 | 97  | 92  | 89  | 94  | 91  | 88  |  | 92  | 89  | 86  |  | 89  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 83  | 89  | 85  | 82  |  | 87  | 84  | 81  |  | 85  |
| 5   | 95  | 87  | 82  | 78  | 93  | 86  | 81  | 77  | 84  | 80  | 77  |  | 83  | 79  | 76  |  | 81  |
| 6   | 91  | 82  | 77  | 73  | 89  | 82  | 76  | 73  | 80  | 76  | 72  |  | 79  | 75  | 72  |  | 78  |
| 7   | 87  | 78  | 73  | 69  | 85  | 77  | 72  | 69  | 76  | 72  | 68  |  | 75  | 71  | 68  |  | 74  |
| 8   | 83  | 74  | 69  | 65  | 82  | 74  | 68  | 65  | 73  | 68  | 65  |  | 72  | 67  | 64  |  | 71  |
| 9   | 79  | 71  | 65  | 62  | 78  | 70  | 65  | 61  | 69  | 65  | 61  |  | 68  | 64  | 61  |  | 68  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  |  | 65  | 61  | 58  |  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203755

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBNWH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 164.9  | 16.6      |
| 10°-20°   | 316.8  | 31.9      |
| 20°-30°   | 288.0  | 29.0      |
| 30°-40°   | 174.6  | 17.6      |
| 40°-50°   | 39.8   | 4.0       |
| 50°-60°   | 5.1    | 0.5       |
| 60°-70°   | 2.3    | 0.2       |
| 70°-80°   | 0.7    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 769.6  | 77.6      |
| 0°-40°    | 944.2  | 95.2      |
| 0°-60°    | 989.1  | 99.7      |
| 0°-90°    | 992.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 992.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1948 |      |
| 5°  | 1836 | 165  |
| 15° | 1141 | 317  |
| 25° | 624  | 288  |
| 35° | 277  | 175  |
| 45° | 44   | 40   |
| 55° | 5    | 5    |
| 65° | 2    | 2    |
| 75° | 0    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P203755

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBNWH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1947.5 |
| 2.5°  | 1923.9 |
| 5°    | 1836.1 |
| 7.5°  | 1694.4 |
| 10°   | 1513.8 |
| 12.5° | 1326.5 |
| 15°   | 1140.8 |
| 17.5° | 972.1  |
| 20°   | 830.3  |
| 22.5° | 715.5  |
| 25°   | 624.4  |
| 27.5° | 543.4  |
| 30°   | 464.1  |
| 32.5° | 371.3  |
| 35°   | 276.8  |
| 37.5° | 194.1  |
| 40°   | 128.3  |
| 42.5° | 79.3   |
| 45°   | 43.9   |
| 47.5° | 20.3   |
| 50°   | 8.4    |
| 52.5° | 6.8    |
| 55°   | 5.1    |
| 57.5° | 5.1    |
| 60°   | 3.4    |
| 62.5° | 3.4    |
| 65°   | 1.7    |
| 67.5° | 1.7    |
| 70°   | 1.7    |
| 72.5° | 1.7    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)