

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205305

Luminaire Tested: **LD6B30D010 EU6B30508030 6LBNLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205305
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508030 6LBNLI1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2349.6 lumens
Efficiency: N/A
Efficacy: 83.9 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205305

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNLI1

Luminous Intensity Polar Plot






TEST NUMBER: P205305

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	112	109	107	112	109	107	106		105	104	102			102	101	99			98
2	109	105	101	98	107	103	100	97		100	97	95			97	95	93			94
3	105	99	94	91	103	97	93	90		95	91	89			93	90	87			90
4	100	93	88	85	98	92	88	84		90	86	83			88	85	82			86
5	96	88	83	79	94	87	83	79		86	82	78			84	81	78			83
6	92	84	79	75	90	83	78	75		82	77	74			80	76	74			79
7	88	80	74	71	87	79	74	71		78	73	70			77	73	70			76
8	84	76	71	67	83	75	70	67		74	70	67			73	69	66			73
9	81	73	67	64	80	72	67	64		71	67	63			70	66	63			70
10	78	69	64	61	77	69	64	61		68	64	61			67	63	60			67

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205305

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	444.8	18.9
10°-20°	798.3	34.0
20°-30°	645.5	27.5
30°-40°	371.8	15.8
40°-50°	78.6	3.3
50°-60°	6.8	0.3
60°-70°	3.4	0.1
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1888.6	80.4
0°-40°	2260.4	96.2
0°-60°	2345.8	99.8
0°-90°	2349.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2349.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5350	
5°	4984	445
15°	2900	798
25°	1392	645
35°	590	372
45°	85	79
55°	7	7
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P205305

CATALOG NUMBER: LD6B30D010 EU6B30508030 6LBNLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	5349.5
2.5°	5285.2
5°	4983.6
7.5°	4550.0
10°	4018.1
12.5°	3472.6
15°	2900.1
17.5°	2347.8
20°	1944.7
22.5°	1636.4
25°	1392.4
27.5°	1185.8
30°	999.4
32.5°	792.8
35°	589.5
37.5°	409.9
40°	267.6
42.5°	162.6
45°	84.7
47.5°	33.9
50°	10.2
52.5°	10.2
55°	6.8
57.5°	6.8
60°	3.4
62.5°	3.4
65°	3.4
67.5°	3.4
70°	3.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)