

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204373

Luminaire Tested: **LD6B20D010 EU6B10209024 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204373
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209024 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1407.0 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204373

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSGPH1

Luminous Intensity Polar Plot






TEST NUMBER: P204373

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	102	99	101	98	96		97	95	93		93
2	102	95	89	84	100	93	88	83	90	85	82		87	83	80		84
3	94	85	78	72	92	83	77	71	80	75	70		78	73	69		75
4	87	76	68	62	85	75	67	62	72	66	61		70	65	60		68
5	80	68	60	54	78	67	60	54	65	59	53		63	58	53		62
6	74	62	54	48	73	61	53	48	59	52	47		58	52	47		56
7	69	57	48	43	68	56	48	43	54	47	42		53	47	42		52
8	65	52	44	38	63	51	44	38	50	43	38		49	42	38		48
9	60	48	40	35	59	47	40	35	46	39	35		45	39	34		44
10	57	44	37	32	56	44	36	32	43	36	31		42	36	31		41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204373

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.5	4.4
10°-20°	172.7	12.3
20°-30°	251.9	17.9
30°-40°	287.2	20.4
40°-50°	275.6	19.6
50°-60°	211.0	15.0
60°-70°	115.8	8.2
70°-80°	30.8	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	486.1	34.5
0°-40°	773.3	55.0
0°-60°	1259.9	89.5
0°-90°	1407.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1407.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	654	
5°	648	62
15°	613	173
25°	547	252
35°	459	287
45°	358	276
55°	236	211
65°	116	116
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P204373

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	653.5
2.5°	651.8
5°	648.4
7.5°	643.3
10°	636.6
12.5°	624.8
15°	612.9
17.5°	599.4
20°	584.2
22.5°	565.7
25°	547.1
27.5°	528.5
30°	504.9
32.5°	482.9
35°	459.3
37.5°	435.6
40°	412.0
42.5°	386.7
45°	358.0
47.5°	329.3
50°	298.9
52.5°	266.8
55°	236.4
57.5°	206.0
60°	173.9
62.5°	143.5
65°	116.5
67.5°	89.5
70°	65.9
72.5°	43.9
75°	27.0
77.5°	11.8
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)