

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204270

Luminaire Tested: **LD6B20D010 EU6B10209024 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204270
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209024 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1541.9 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204270

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204270

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	104	101	108	105	102	99	101	98	96		97	95	93		94
2	103	96	90	85	100	94	89	84	91	86	83		87	84	81		85
3	95	86	79	73	93	84	78	73	82	76	72		79	74	70		76
4	88	77	70	64	86	76	69	63	74	68	63		72	66	62		69
5	81	70	62	56	79	69	62	56	67	60	55		65	59	55		63
6	76	64	56	50	74	63	55	50	61	54	49		60	54	49		58
7	71	58	51	45	69	58	50	45	56	49	45		55	49	44		54
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204270

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.8	5.5
10°-20°	219.5	14.2
20°-30°	287.1	18.6
30°-40°	304.0	19.7
40°-50°	283.6	18.4
50°-60°	214.8	13.9
60°-70°	116.3	7.5
70°-80°	31.2	2.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	591.5	38.4
0°-40°	895.5	58.1
0°-60°	1393.9	90.4
0°-90°	1541.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1541.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	920	
5°	906	85
15°	785	220
25°	624	287
35°	486	304
45°	370	284
55°	241	215
65°	116	116
75°	27	31
85°	0	0
90°	0	



TEST NUMBER: P204270

CATALOG NUMBER: LD6B20D010 EU6B10209024 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	919.6
2.5°	916.2
5°	906.1
7.5°	884.2
10°	855.5
12.5°	821.7
15°	784.6
17.5°	742.4
20°	705.3
22.5°	663.1
25°	624.3
27.5°	585.5
30°	548.4
32.5°	516.3
35°	485.9
37.5°	455.6
40°	426.9
42.5°	398.2
45°	369.5
47.5°	337.5
50°	305.4
52.5°	273.3
55°	241.3
57.5°	207.5
60°	175.5
62.5°	145.1
65°	116.4
67.5°	89.4
70°	65.8
72.5°	45.6
75°	27.0
77.5°	11.8
80°	3.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)