

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204388

Luminaire Tested: **LD6B30D010 EU6B30509030 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204388
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509030 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2411.4 lumens
Efficiency: N/A
Efficacy: 86.1 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204388

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204388

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	111	107	103	100	108	105	102	99	101	98	96		97	95	93		93
2	102	95	89	84	100	93	88	83	90	85	82		87	83	80		84
3	94	85	78	72	92	83	77	71	80	75	70		78	73	69		75
4	87	76	68	62	85	75	67	62	72	66	61		70	65	60		68
5	80	68	60	54	78	67	60	54	65	59	53		63	58	53		62
6	74	62	54	48	73	61	53	48	59	52	47		58	52	47		56
7	69	57	48	43	68	56	48	43	54	47	42		53	47	42		52
8	65	52	44	38	63	51	44	38	50	43	38		49	42	38		48
9	60	48	40	35	59	47	40	35	46	39	35		45	39	34		44
10	57	44	37	32	56	44	36	32	43	36	31		42	36	31		41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204388

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.4	4.4
10°-20°	296.0	12.3
20°-30°	431.7	17.9
30°-40°	492.3	20.4
40°-50°	472.2	19.6
50°-60°	361.7	15.0
60°-70°	198.5	8.2
70°-80°	52.8	2.2
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.1	34.6
0°-40°	1325.4	55.0
0°-60°	2159.3	89.5
0°-90°	2411.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2411.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1120	
5°	1111	105
15°	1050	296
25°	938	432
35°	787	492
45°	614	472
55°	405	362
65°	200	198
75°	46	53
85°	0	1
90°	0	



TEST NUMBER: P204388

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1120.0
2.5°	1117.1
5°	1111.3
7.5°	1102.6
10°	1091.0
12.5°	1070.8
15°	1050.5
17.5°	1027.4
20°	1001.3
22.5°	969.5
25°	937.6
27.5°	905.8
30°	865.3
32.5°	827.7
35°	787.2
37.5°	746.6
40°	706.1
42.5°	662.7
45°	613.5
47.5°	564.3
50°	512.2
52.5°	457.2
55°	405.2
57.5°	353.1
60°	298.1
62.5°	246.0
65°	199.7
67.5°	153.4
70°	112.9
72.5°	75.2
75°	46.3
77.5°	20.3
80°	5.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)