

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204285

Luminaire Tested: **LD6B30D010 EU6B30509030 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509030 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2642.7 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204285

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204285

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101	108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85	100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73	93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64	86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56	79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50	74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45	69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41	65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37	61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34	57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204285

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.4	5.5
10°-20°	376.3	14.2
20°-30°	492.1	18.6
30°-40°	521.1	19.7
40°-50°	486.0	18.4
50°-60°	368.1	13.9
60°-70°	199.4	7.5
70°-80°	53.5	2.0
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1013.8	38.4
0°-40°	1534.9	58.1
0°-60°	2389.0	90.4
0°-90°	2642.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2642.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1576	
5°	1553	145
15°	1345	376
25°	1070	492
35°	833	521
45°	633	486
55°	414	368
65°	200	199
75°	46	53
85°	0	1
90°	0	



TEST NUMBER: P204285

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBSWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1576.1
2.5°	1570.3
5°	1553.0
7.5°	1515.4
10°	1466.2
12.5°	1408.4
15°	1344.7
17.5°	1272.4
20°	1208.8
22.5°	1136.5
25°	1070.0
27.5°	1003.5
30°	939.9
32.5°	884.9
35°	832.9
37.5°	780.8
40°	731.7
42.5°	682.5
45°	633.3
47.5°	578.4
50°	523.4
52.5°	468.5
55°	413.5
57.5°	355.7
60°	300.8
62.5°	248.7
65°	199.5
67.5°	153.3
70°	112.8
72.5°	78.1
75°	46.3
77.5°	20.2
80°	5.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)