

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202740

Luminaire Tested: **LD6B30D010 EU6B30509030 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202740
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509030 6LBWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2232.1 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202740

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202740

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	103	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81
4	92	82	75	70	90	81	75	70	79	73	69		77	72	68		75
5	86	75	68	63	84	74	68	63	72	66	62		71	65	61		69
6	80	69	62	57	78	68	61	56	67	61	56		65	60	56		64
7	75	64	56	51	73	63	56	51	62	55	51		60	55	51		59
8	70	59	52	47	69	58	51	47	57	51	46		56	50	46		55
9	66	55	48	43	65	54	47	43	53	47	43		52	47	42		51
10	62	51	44	40	61	50	44	39	50	43	39		49	43	39		48

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202740

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.0	5.8
10°-20°	369.0	16.5
20°-30°	541.0	24.2
30°-40°	563.0	25.2
40°-50°	389.5	17.5
50°-60°	169.6	7.6
60°-70°	52.0	2.3
70°-80°	15.6	0.7
80°-90°	2.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1040.0	46.6
0°-40°	1603.0	71.8
0°-60°	2162.2	96.9
0°-90°	2232.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2232.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1377	
5°	1371	130
15°	1310	369
25°	1183	541
35°	911	563
45°	503	390
55°	182	170
65°	49	52
75°	14	16
85°	3	2
90°	0	



TEST NUMBER: P202740

CATALOG NUMBER: LD6B30D010 EU6B30509030 6LBWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1376.8
2.5°	1379.6
5°	1371.0
7.5°	1359.4
10°	1344.9
12.5°	1330.5
15°	1310.2
17.5°	1284.2
20°	1255.3
22.5°	1223.5
25°	1183.0
27.5°	1130.9
30°	1064.4
32.5°	995.0
35°	911.1
37.5°	818.5
40°	711.5
42.5°	604.5
45°	503.3
47.5°	407.8
50°	323.9
52.5°	245.8
55°	182.2
57.5°	130.2
60°	89.7
62.5°	66.5
65°	49.2
67.5°	37.6
70°	26.0
72.5°	20.2
75°	14.5
77.5°	8.7
80°	5.8
82.5°	2.9
85°	2.9
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)