

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203853

Luminaire Tested: **LD6B20D010 EU6B10208027 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203853
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208027 6LBNGPH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 980.7 lumens
Efficiency: N/A
Efficacy: 47.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203853

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203853

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203853

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.9	11.0
10°-20°	266.2	27.1
20°-30°	322.5	32.9
30°-40°	219.8	22.4
40°-50°	52.3	5.3
50°-60°	8.2	0.8
60°-70°	3.0	0.3
70°-80°	0.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	696.5	71.0
0°-40°	916.3	93.4
0°-60°	976.8	99.6
0°-90°	980.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	980.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1192	
5°	1159	108
15°	953	266
25°	704	322
35°	351	220
45°	56	52
55°	9	8
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203853

CATALOG NUMBER: LD6B20D010 EU6B10208027 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1192.1
2.5°	1185.4
5°	1158.6
7.5°	1122.8
10°	1071.3
12.5°	1013.2
15°	952.8
17.5°	890.2
20°	827.5
22.5°	764.9
25°	704.5
27.5°	648.6
30°	568.1
32.5°	463.0
35°	351.1
37.5°	250.5
40°	165.5
42.5°	102.9
45°	55.9
47.5°	29.1
50°	15.7
52.5°	11.2
55°	8.9
57.5°	6.7
60°	4.5
62.5°	4.5
65°	2.2
67.5°	2.2
70°	2.2
72.5°	2.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)