

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203054

Luminaire Tested: **LD6B30D010 EU6B30509730 6LBWB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203054
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509730 6LBWB1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1240.9 lumens
Efficiency: N/A
Efficacy: 44.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203054

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWB1

Luminous Intensity Polar Plot






TEST NUMBER: P203054

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	73		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	83	73	67	62	82	72	66	61	71	65	61		69	64	61		68
7	78	68	61	56	77	67	61	56	66	60	56		65	60	56		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	52	48	69	58	52	48	57	52	48		57	51	47		56
10	66	55	49	44	65	55	49	44	54	48	44		53	48	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203054

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	7.1
10°-20°	245.9	19.8
20°-30°	344.4	27.8
30°-40°	329.0	26.5
40°-50°	187.3	15.1
50°-60°	45.8	3.7
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	678.3	54.7
0°-40°	1007.2	81.2
0°-60°	1240.3	100.0
0°-90°	1240.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1240.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	935	
5°	928	88
15°	872	246
25°	753	344
35°	536	329
45°	240	187
55°	46	46
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203054

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	935.2
2.5°	935.2
5°	927.7
7.5°	917.5
10°	910.0
12.5°	894.8
15°	872.0
17.5°	851.8
20°	826.6
22.5°	793.7
25°	753.2
27.5°	707.8
30°	657.2
32.5°	596.5
35°	535.9
37.5°	462.6
40°	384.2
42.5°	310.9
45°	240.1
47.5°	176.9
50°	123.9
52.5°	78.4
55°	45.5
57.5°	20.2
60°	5.1
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)