

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202951

Luminaire Tested: **LD6B30D010 EU6B30509730 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202951
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509730 6LBWGPH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1468.4 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202951

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P202951

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82
4	93	84	77	72	91	82	76	72	80	75	71		78	74	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	81	71	64	59	80	70	63	59	68	62	58		67	62	58		65
7	76	65	58	53	75	65	58	53	63	57	53		62	57	53		61
8	72	61	54	49	70	60	53	49	59	53	49		58	52	48		57
9	68	57	50	45	66	56	49	45	55	49	45		54	48	45		53
10	64	53	46	42	63	52	46	42	51	45	41		51	45	41		50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202951

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.0	6.4
10°-20°	263.6	18.0
20°-30°	377.2	25.7
30°-40°	376.0	25.6
40°-50°	239.5	16.3
50°-60°	88.3	6.0
60°-70°	22.1	1.5
70°-80°	6.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	734.9	50.0
0°-40°	1110.8	75.7
0°-60°	1438.6	98.0
0°-90°	1468.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1468.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	998	
5°	993	94
15°	937	264
25°	824	377
35°	611	376
45°	308	239
55°	94	88
65°	20	22
75°	5	7
85°	0	1
90°	0	



TEST NUMBER: P202951

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	998.0
2.5°	998.0
5°	992.9
7.5°	982.8
10°	970.2
12.5°	955.0
15°	937.4
17.5°	914.6
20°	889.4
22.5°	861.6
25°	823.7
27.5°	783.2
30°	730.2
32.5°	674.6
35°	611.4
37.5°	535.6
40°	457.3
42.5°	381.5
45°	308.2
47.5°	242.6
50°	181.9
52.5°	133.9
55°	93.5
57.5°	60.6
60°	40.4
62.5°	27.8
65°	20.2
67.5°	15.2
70°	12.6
72.5°	7.6
75°	5.1
77.5°	5.1
80°	2.5
82.5°	2.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)