

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202848

Luminaire Tested: **LD6B30D010 EU6B30509730 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202848
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30509730 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2016.8 lumens
Efficiency: N/A
Efficacy: 72.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202848

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202848

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	109	107	104	110	107	105	102		103	101	99			99	98	96			96
2	106	100	96	92	104	98	94	91		95	92	89			92	89	87			89
3	99	92	86	81	97	90	85	81		88	83	79			85	81	78			83
4	93	84	78	73	91	83	77	72		81	76	71			79	74	71			77
5	87	77	71	66	85	76	70	65		75	69	65			73	68	64			71
6	82	71	64	59	80	71	64	59		69	63	59			67	62	58			66
7	77	66	59	54	75	65	59	54		64	58	54			63	57	53			61
8	72	61	54	49	71	61	54	49		59	53	49			58	53	49			57
9	68	57	50	45	67	56	50	45		55	49	45			54	49	45			53
10	64	53	46	42	63	53	46	42		52	46	42			51	45	42			50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202848

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.4	6.0
10°-20°	358.1	17.8
20°-30°	539.0	26.7
30°-40°	551.1	27.3
40°-50°	334.7	16.6
50°-60°	94.2	4.7
60°-70°	14.3	0.7
70°-80°	4.7	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1017.5	50.4
0°-40°	1568.6	77.8
0°-60°	1997.5	99.0
0°-90°	2016.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2016.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1253	
5°	1258	120
15°	1268	358
25°	1177	539
35°	893	551
45°	430	335
55°	94	94
65°	13	14
75°	5	5
85°	0	0
90°	0	



TEST NUMBER: P202848

CATALOG NUMBER: LD6B30D010 EU6B30509730 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1252.7
2.5°	1252.7
5°	1257.7
7.5°	1265.3
10°	1265.3
12.5°	1270.4
15°	1267.9
17.5°	1262.8
20°	1245.1
22.5°	1219.8
25°	1176.7
27.5°	1128.7
30°	1062.9
32.5°	984.4
35°	893.3
37.5°	792.1
40°	675.7
42.5°	554.2
45°	430.2
47.5°	318.9
50°	225.2
52.5°	151.8
55°	93.6
57.5°	55.7
60°	27.8
62.5°	17.7
65°	12.7
67.5°	10.1
70°	7.6
72.5°	5.1
75°	5.1
77.5°	2.5
80°	2.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)