

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203344

Luminaire Tested: **LD6B20D010 EU6B10209027 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203344
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209027 6LBMWH1
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1321.0 lumens
Efficiency: N/A
Efficacy: 63.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203344

CATALOG NUMBER: LD6B20D010 EU6B10209027 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203344

CATALOG NUMBER: LD6B20D010 EU6B10209027 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	108	106	111	109	106	104		105	103	101			101	100	98			97
2	108	103	99	96	106	101	98	95		98	95	93			95	93	91			93
3	103	96	91	87	101	95	90	87		92	88	85			90	87	84			88
4	97	90	85	80	96	89	84	80		87	82	79			85	81	78			83
5	93	84	79	74	91	83	78	74		82	77	73			80	76	73			78
6	88	79	73	69	87	78	73	69		77	72	68			76	71	68			74
7	84	75	69	64	82	74	68	64		73	68	64			71	67	64			70
8	80	70	64	60	78	70	64	60		69	64	60			68	63	60			67
9	76	66	61	57	75	66	60	57		65	60	56			64	59	56			63
10	72	63	57	53	71	62	57	53		62	57	53			61	56	53			60

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203344

CATALOG NUMBER: LD6B20D010 EU6B10209027 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	11.4
10°-20°	369.9	28.0
20°-30°	428.0	32.4
30°-40°	273.5	20.7
40°-50°	77.6	5.9
50°-60°	13.9	1.0
60°-70°	5.7	0.4
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	948.5	71.8
0°-40°	1222.1	92.5
0°-60°	1313.5	99.4
0°-90°	1321.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1321.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1648	
5°	1619	151
15°	1326	370
25°	944	428
35°	432	274
45°	90	78
55°	13	14
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203344

CATALOG NUMBER: LD6B20D010 EU6B10209027 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1648.1
2.5°	1646.2
5°	1618.7
7.5°	1569.1
10°	1499.2
12.5°	1418.4
15°	1326.5
17.5°	1231.0
20°	1137.3
22.5°	1045.4
25°	944.4
27.5°	834.1
30°	711.0
32.5°	573.2
35°	431.8
37.5°	312.3
40°	216.8
42.5°	143.3
45°	90.0
47.5°	53.3
50°	31.2
52.5°	18.4
55°	12.9
57.5°	11.0
60°	9.2
62.5°	7.3
65°	5.5
67.5°	3.7
70°	3.7
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)