

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203349

Luminaire Tested: **LD6B20D010 EU6B10209727 6LBMWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203349  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6B20D010 EU6B10209727 6LBMWH1  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
MEDIUM DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1149.1 lumens  
Efficiency: N/A  
Efficacy: 55.2 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203349

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBMWH1

### Luminous Intensity Polar Plot






TEST NUMBER: P203349

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBMWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 |  | 101 | 100 | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 95  | 98  | 95  | 93  |  | 95  | 93  | 91  |  | 92  |
| 3   | 103 | 96  | 91  | 87  | 101 | 95  | 90  | 87  | 92  | 88  | 85  |  | 90  | 87  | 84  |  | 88  |
| 4   | 97  | 90  | 85  | 80  | 96  | 89  | 84  | 80  | 87  | 82  | 79  |  | 85  | 81  | 78  |  | 83  |
| 5   | 93  | 84  | 79  | 74  | 91  | 83  | 78  | 74  | 82  | 77  | 73  |  | 80  | 76  | 73  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 87  | 78  | 73  | 69  | 77  | 72  | 68  |  | 76  | 71  | 68  |  | 74  |
| 7   | 84  | 75  | 69  | 64  | 82  | 74  | 68  | 64  | 73  | 68  | 64  |  | 71  | 67  | 64  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 64  | 60  |  | 68  | 63  | 60  |  | 67  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 57  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203349

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBMWH1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 131.0  | 11.4      |
| 10°-20°   | 321.7  | 28.0      |
| 20°-30°   | 372.2  | 32.4      |
| 30°-40°   | 237.9  | 20.7      |
| 40°-50°   | 67.5   | 5.9       |
| 50°-60°   | 12.1   | 1.0       |
| 60°-70°   | 4.9    | 0.4       |
| 70°-80°   | 1.7    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 825.0  | 71.8      |
| 0°-40°    | 1062.9 | 92.5      |
| 0°-60°    | 1142.5 | 99.4      |
| 0°-90°    | 1149.1 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1149.1 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1434 |      |
| 5°  | 1408 | 131  |
| 15° | 1154 | 322  |
| 25° | 821  | 372  |
| 35° | 376  | 238  |
| 45° | 78   | 67   |
| 55° | 11   | 12   |
| 65° | 5    | 5    |
| 75° | 2    | 2    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P203349

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBMWH1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1433.5 |
| 2.5°  | 1431.9 |
| 5°    | 1407.9 |
| 7.5°  | 1364.8 |
| 10°   | 1304.0 |
| 12.5° | 1233.7 |
| 15°   | 1153.8 |
| 17.5° | 1070.7 |
| 20°   | 989.2  |
| 22.5° | 909.3  |
| 25°   | 821.4  |
| 27.5° | 725.5  |
| 30°   | 618.5  |
| 32.5° | 498.6  |
| 35°   | 375.5  |
| 37.5° | 271.7  |
| 40°   | 188.6  |
| 42.5° | 124.7  |
| 45°   | 78.3   |
| 47.5° | 46.3   |
| 50°   | 27.2   |
| 52.5° | 16.0   |
| 55°   | 11.2   |
| 57.5° | 9.6    |
| 60°   | 8.0    |
| 62.5° | 6.4    |
| 65°   | 4.8    |
| 67.5° | 3.2    |
| 70°   | 3.2    |
| 72.5° | 1.6    |
| 75°   | 1.6    |
| 77.5° | 1.6    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)