

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204486

Luminaire Tested: **LD6B30D010 EU6B30508035 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204486
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508035 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2772.0 lumens
Efficiency: N/A
Efficacy: 99.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204486

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBSB1

Luminous Intensity Polar Plot






TEST NUMBER: P204486

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88		
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76		
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65		
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57		
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50		
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44		
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39		
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35		
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32		
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204486

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.4	4.2
10°-20°	327.5	11.8
20°-30°	487.1	17.6
30°-40°	566.9	20.4
40°-50°	552.5	19.9
50°-60°	425.0	15.3
60°-70°	234.9	8.5
70°-80°	62.2	2.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	930.0	33.6
0°-40°	1496.9	54.0
0°-60°	2474.4	89.3
0°-90°	2772.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2772.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1223	
5°	1216	115
15°	1160	327
25°	1058	487
35°	910	567
45°	717	553
55°	474	425
65°	235	235
75°	53	62
85°	0	0
90°	0	



TEST NUMBER: P204486

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1222.9
2.5°	1222.9
5°	1215.8
7.5°	1205.3
10°	1198.3
12.5°	1177.2
15°	1159.6
17.5°	1142.0
20°	1117.4
22.5°	1092.8
25°	1057.7
27.5°	1022.6
30°	987.4
32.5°	948.8
35°	910.1
37.5°	860.9
40°	818.8
42.5°	773.1
45°	716.8
47.5°	664.1
50°	604.4
52.5°	541.1
55°	474.4
57.5°	411.1
60°	351.4
62.5°	291.7
65°	235.4
67.5°	182.7
70°	133.5
72.5°	91.4
75°	52.7
77.5°	24.6
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)