

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204379

Luminaire Tested: **LD6B20D010 EU6B10209727 6LBSGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204379
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209727 6LBSGPH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1390.9 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.26
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204379

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBSGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P204379

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBSGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100		108	105	102	99		101	98	96		97	95	93		93	91	90
2	102	95	89	84		100	93	88	83		90	85	82		87	83	80		84	81	78
3	94	85	78	72		92	83	77	71		80	75	70		78	73	69		75	71	68
4	87	76	68	62		85	75	67	62		72	66	61		70	65	60		68	63	59
5	80	68	60	54		78	67	60	54		65	59	53		63	58	53		62	56	52
6	74	62	54	48		73	61	53	48		59	52	47		58	52	47		56	51	47
7	69	57	48	43		68	56	48	43		54	47	42		53	47	42		52	46	42
8	65	52	44	38		63	51	44	38		50	43	38		49	42	38		48	42	38
9	60	48	40	35		59	47	40	35		46	39	35		45	39	34		44	38	34
10	57	44	37	32		56	44	36	32		43	36	31		42	36	31		41	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204379

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBSGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.8	4.4
10°-20°	170.7	12.3
20°-30°	249.0	17.9
30°-40°	284.0	20.4
40°-50°	272.4	19.6
50°-60°	208.6	15.0
60°-70°	114.5	8.2
70°-80°	30.4	2.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.6	34.6
0°-40°	764.5	55.0
0°-60°	1245.5	89.5
0°-90°	1390.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1390.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	646	
5°	641	61
15°	606	171
25°	541	249
35°	454	284
45°	354	272
55°	234	209
65°	115	114
75°	27	30
85°	0	0
90°	0	



TEST NUMBER: P204379

CATALOG NUMBER: LD6B20D010 EU6B10209727 6LBSGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	646.0
2.5°	644.3
5°	641.0
7.5°	636.0
10°	629.3
12.5°	617.6
15°	605.9
17.5°	592.6
20°	577.6
22.5°	559.2
25°	540.8
27.5°	522.5
30°	499.1
32.5°	477.4
35°	454.0
37.5°	430.7
40°	407.3
42.5°	382.3
45°	353.9
47.5°	325.5
50°	295.5
52.5°	263.7
55°	233.7
57.5°	203.6
60°	171.9
62.5°	141.9
65°	115.2
67.5°	88.5
70°	65.1
72.5°	43.4
75°	26.7
77.5°	11.7
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)