

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202529

Luminaire Tested: **LD6B30D010 EU6B30508035 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202529
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508035 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3182.4 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202529

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBSWMH1

Luminous Intensity Polar Plot






TEST NUMBER: P202529

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101	108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85	100	94	89	84		91	86	82		87	84	81		84	81	79
3	95	86	79	73	92	84	78	73		81	76	71		79	74	70		76	72	69
4	88	77	70	64	86	76	69	63		74	67	62		71	66	62		69	65	61
5	81	70	62	56	79	69	61	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50	74	63	55	50		61	54	49		59	53	49		58	53	48
7	70	58	50	45	69	57	50	45		56	49	44		55	48	44		53	48	44
8	66	54	46	40	64	53	45	40		52	45	40		50	44	40		49	44	40
9	62	49	42	37	61	49	42	37		48	41	37		47	41	36		46	40	36
10	58	46	39	34	57	45	38	34		45	38	34		44	38	33		43	37	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202529

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.3	5.4
10°-20°	445.1	14.0
20°-30°	590.2	18.5
30°-40°	629.5	19.8
40°-50°	588.4	18.5
50°-60°	448.7	14.1
60°-70°	244.1	7.7
70°-80°	65.4	2.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1205.5	37.9
0°-40°	1835.0	57.7
0°-60°	2872.1	90.2
0°-90°	3182.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3182.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1840	
5°	1815	170
15°	1587	445
25°	1285	590
35°	1006	629
45°	766	588
55°	505	449
65°	244	244
75°	56	65
85°	0	1
90°	0	



TEST NUMBER: P202529

CATALOG NUMBER: LD6B30D010 EU6B30508035 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1840.3
2.5°	1834.4
5°	1814.9
7.5°	1774.0
10°	1727.2
12.5°	1660.9
15°	1586.8
17.5°	1512.8
20°	1432.8
22.5°	1356.8
25°	1284.7
27.5°	1208.7
30°	1136.5
32.5°	1066.3
35°	1005.9
37.5°	945.5
40°	883.1
42.5°	826.6
45°	766.1
47.5°	699.8
50°	637.5
52.5°	571.2
55°	504.9
57.5°	432.8
60°	366.5
62.5°	304.1
65°	243.7
67.5°	189.1
70°	138.4
72.5°	95.5
75°	56.5
77.5°	25.3
80°	5.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)