

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204888

Luminaire Tested: **LD6B20D010 EU6B10208040 6LBCSMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208040 6LBCSMB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1959.0 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204888

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBCSMB1

Luminous Intensity Polar Plot





TEST NUMBER: P204888

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBCSMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	104	101	98		100	98	95		96	94	92		93	91	90
2	102	95	89	84	99	93	87	83		89	85	81		86	82	79		83	80	77
3	93	84	77	71	91	83	76	70		80	74	69		77	72	68		74	70	67
4	86	75	67	61	84	74	66	61		71	65	60		69	63	59		67	62	58
5	79	67	59	53	77	66	59	53		64	57	52		62	56	52		61	55	51
6	74	61	53	47	72	60	52	46		58	51	46		57	50	46		55	50	45
7	68	55	47	41	67	55	47	41		53	46	41		52	45	41		50	45	40
8	64	51	43	37	62	50	42	37		49	42	37		48	41	37		46	41	36
9	60	47	39	33	58	46	39	33		45	38	33		44	38	33		43	37	33
10	56	43	35	30	55	43	35	30		42	35	30		41	34	30		40	34	30

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204888

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBCSMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	4.0
10°-20°	222.9	11.4
20°-30°	335.1	17.1
30°-40°	397.6	20.3
40°-50°	393.4	20.1
50°-60°	309.1	15.8
60°-70°	173.3	8.8
70°-80°	48.6	2.5
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	636.3	32.5
0°-40°	1033.8	52.8
0°-60°	1736.3	88.6
0°-90°	1959.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1959.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	827	
5°	826	78
15°	791	223
25°	728	335
35°	638	398
45°	513	393
55°	348	309
65°	173	173
75°	42	49
85°	0	1
90°	0	



TEST NUMBER: P204888

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBCSMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	827.2
2.5°	824.4
5°	825.8
7.5°	818.8
10°	810.4
12.5°	800.5
15°	790.7
17.5°	778.1
20°	761.2
22.5°	744.4
25°	727.5
27.5°	709.3
30°	685.4
32.5°	661.5
35°	637.6
37.5°	609.5
40°	577.2
42.5°	546.3
45°	512.6
47.5°	474.7
50°	435.4
52.5°	390.4
55°	348.3
57.5°	300.6
60°	255.6
62.5°	214.9
65°	172.7
67.5°	136.2
70°	101.1
72.5°	68.8
75°	42.1
77.5°	21.1
80°	5.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)