

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205410

Luminaire Tested: **LD6B30D010 EU6B30508050 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205410
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508050 6LBSLI1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3298.2 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205410

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205410

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	101	109	105	102	99		101	99	96			97	95	93			94
2	103	96	91	86	100	94	89	85		91	87	83			88	84	81			85
3	95	86	79	74	93	85	78	73		82	76	72			79	75	71			77
4	88	78	70	64	86	77	69	64		74	68	63			72	67	62			70
5	82	71	63	57	80	70	62	57		67	61	56			66	60	55			64
6	76	64	56	51	74	63	56	51		62	55	50			60	54	50			59
7	71	59	51	46	70	58	51	45		57	50	45			55	49	45			54
8	67	54	47	41	65	54	46	41		52	46	41			51	45	41			50
9	63	50	43	38	61	50	43	38		49	42	38			48	42	37			47
10	59	47	40	35	58	46	39	35		45	39	35			45	39	34			44

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205410

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	5.8
10°-20°	488.2	14.8
20°-30°	622.6	18.9
30°-40°	645.7	19.6
40°-50°	595.0	18.0
50°-60°	447.5	13.6
60°-70°	241.6	7.3
70°-80°	64.8	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1302.6	39.5
0°-40°	1948.3	59.1
0°-60°	2990.8	90.7
0°-90°	3298.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3298.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2081	
5°	2050	192
15°	1741	488
25°	1352	623
35°	1030	646
45°	774	595
55°	501	448
65°	242	242
75°	56	65
85°	0	1
90°	0	



TEST NUMBER: P205410

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSLI1

CANDELA DISTRIBUTION (FULL):

0°	
0°	2081.3
2.5°	2074.3
5°	2049.8
7.5°	2004.2
10°	1923.6
12.5°	1843.0
15°	1741.4
17.5°	1646.8
20°	1548.7
22.5°	1447.1
25°	1352.5
27.5°	1261.4
30°	1177.3
32.5°	1100.2
35°	1030.1
37.5°	963.6
40°	900.5
42.5°	833.9
45°	774.4
47.5°	707.8
50°	641.2
52.5°	571.1
55°	501.1
57.5°	431.0
60°	364.4
62.5°	301.3
65°	241.8
67.5°	185.7
70°	136.7
72.5°	94.6
75°	56.1
77.5°	24.5
80°	7.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)