

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203135

Luminaire Tested: **LD6B20D010 EU6B10208040 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203135
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10208040 6LBWMW1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1995.3 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203135

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203135

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	111	107	104	100	108	105	102	99		101	98	96			97	95	93			93
2	103	96	90	86	100	94	89	85		91	86	83			88	84	81			85
3	95	86	80	74	93	85	79	74		82	77	72			80	75	71			77
4	89	78	71	65	86	77	70	65		75	69	64			72	67	63			70
5	82	71	64	58	80	70	63	58		68	62	57			66	61	56			65
6	77	65	57	52	75	64	57	52		63	56	51			61	55	51			60
7	72	60	52	47	70	59	52	47		58	51	46			56	50	46			55
8	67	55	48	42	66	55	47	42		53	47	42			52	46	42			51
9	63	51	44	39	62	51	44	39		50	43	39			49	43	38			48
10	60	48	40	36	58	47	40	36		46	40	36			45	40	35			45

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203135

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.5	5.3
10°-20°	295.9	14.8
20°-30°	426.4	21.4
30°-40°	442.7	22.2
40°-50°	327.3	16.4
50°-60°	195.5	9.8
60°-70°	118.8	6.0
70°-80°	65.1	3.3
80°-90°	18.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	827.8	41.5
0°-40°	1270.5	63.7
0°-60°	1793.3	89.9
0°-90°	1995.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1995.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1120	
5°	1113	106
15°	1050	296
25°	929	426
35°	714	443
45°	421	327
55°	213	196
65°	119	119
75°	60	65
85°	14	18
90°	0	



TEST NUMBER: P203135

CATALOG NUMBER: LD6B20D010 EU6B10208040 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1120.5
2.5°	1120.5
5°	1113.2
7.5°	1103.5
10°	1089.0
12.5°	1072.1
15°	1050.3
17.5°	1026.1
20°	1001.9
22.5°	968.0
25°	929.3
27.5°	888.2
30°	834.9
32.5°	781.7
35°	713.9
37.5°	643.7
40°	566.3
42.5°	491.3
45°	421.1
47.5°	358.2
50°	302.5
52.5°	254.1
55°	213.0
57.5°	181.5
60°	154.9
62.5°	135.5
65°	118.6
67.5°	104.1
70°	89.5
72.5°	75.0
75°	60.5
77.5°	48.4
80°	36.3
82.5°	26.6
85°	14.5
87.5°	7.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)