

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204282

Luminaire Tested: **LD6B30D010 EU6B30508050 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204282
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508050 6LBSWH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3203.5 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204282

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSWH1

Luminous Intensity Polar Plot






TEST NUMBER: P204282

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101		108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85		100	94	89	84		91	86	83		87	84	81		85	82	79
3	95	86	79	73		93	84	78	73		82	76	72		79	74	70		76	73	69
4	88	77	70	64		86	76	69	63		74	68	63		72	66	62		69	65	61
5	81	70	62	56		79	69	62	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50		74	63	55	50		61	54	49		60	54	49		58	53	49
7	71	58	51	45		69	58	50	45		56	49	45		55	49	44		54	48	44
8	66	54	46	41		65	53	46	41		52	45	40		51	45	40		50	44	40
9	62	50	42	37		61	49	42	37		48	41	37		47	41	37		46	41	37
10	58	46	39	34		57	46	39	34		45	38	34		44	38	34		43	38	34

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204282

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	176.2	5.5
10°-20°	456.1	14.2
20°-30°	596.6	18.6
30°-40°	631.7	19.7
40°-50°	589.2	18.4
50°-60°	446.2	13.9
60°-70°	241.7	7.5
70°-80°	64.8	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1228.9	38.4
0°-40°	1860.6	58.1
0°-60°	2896.0	90.4
0°-90°	3203.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3203.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1911	
5°	1882	176
15°	1630	456
25°	1297	597
35°	1010	632
45°	768	589
55°	501	446
65°	242	242
75°	56	65
85°	0	1
90°	0	



TEST NUMBER: P204282

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1910.6
2.5°	1903.5
5°	1882.5
7.5°	1836.9
10°	1777.3
12.5°	1707.2
15°	1630.1
17.5°	1542.5
20°	1465.3
22.5°	1377.7
25°	1297.1
27.5°	1216.4
30°	1139.3
32.5°	1072.7
35°	1009.6
37.5°	946.5
40°	886.9
42.5°	827.3
45°	767.7
47.5°	701.1
50°	634.5
52.5°	567.9
55°	501.3
57.5°	431.2
60°	364.6
62.5°	301.5
65°	241.9
67.5°	185.8
70°	136.7
72.5°	94.7
75°	56.1
77.5°	24.5
80°	7.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)