

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202531

Luminaire Tested: **LD6B30D010 EU6B30508050 6LBSWMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202531
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508050 6LBSWMH1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH WARM HAZE TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3215.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 1.1
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202531

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSWMH1

Luminous Intensity Polar Plot






TEST NUMBER: P202531

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSWMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	104	101	108	105	102	99		101	98	96		97	95	93		94	92	90
2	103	96	90	85	100	94	89	84		91	86	82		87	84	81		84	81	79
3	95	86	79	73	92	84	78	73		81	76	71		79	74	70		76	72	69
4	88	77	70	64	86	76	69	63		74	67	62		71	66	62		69	65	61
5	81	70	62	56	79	69	61	56		67	60	55		65	59	55		63	58	54
6	76	64	56	50	74	63	55	50		61	54	49		59	53	49		58	53	48
7	70	58	50	45	69	57	50	45		56	49	44		55	48	44		53	48	44
8	66	54	46	40	64	53	45	40		52	45	40		50	44	40		49	44	40
9	62	49	42	37	61	49	42	37		48	41	37		47	41	36		46	40	36
10	58	46	39	34	57	45	38	34		45	38	34		44	38	33		43	37	33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202531

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSWMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.0	5.4
10°-20°	449.6	14.0
20°-30°	596.2	18.5
30°-40°	635.9	19.8
40°-50°	594.5	18.5
50°-60°	453.3	14.1
60°-70°	246.5	7.7
70°-80°	66.1	2.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1217.8	37.9
0°-40°	1853.8	57.7
0°-60°	2901.5	90.2
0°-90°	3215.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3215.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1859	
5°	1834	172
15°	1603	450
25°	1298	596
35°	1016	636
45°	774	594
55°	510	453
65°	246	247
75°	57	66
85°	0	1
90°	0	



TEST NUMBER: P202531

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBSWMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1859.1
2.5°	1853.2
5°	1833.5
7.5°	1792.1
10°	1744.9
12.5°	1677.9
15°	1603.1
17.5°	1528.3
20°	1447.5
22.5°	1370.7
25°	1297.8
27.5°	1221.0
30°	1148.2
32.5°	1077.3
35°	1016.2
37.5°	955.2
40°	892.1
42.5°	835.0
45°	774.0
47.5°	707.0
50°	644.0
52.5°	577.0
55°	510.1
57.5°	437.2
60°	370.2
62.5°	307.2
65°	246.2
67.5°	191.0
70°	139.8
72.5°	96.5
75°	57.1
77.5°	25.6
80°	5.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)