

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202840

Luminaire Tested: **LD6B30D010 EU6B30508050 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B30D010 EU6B30508050 6LBWWH1
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-27.4 W DE010-27.95 W D5LT-27.65 W DMX-27.73 W DL2-29.56 W
DL3-29.67 W DLE-29.73 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2796.9 lumens
Efficiency: N/A
Efficacy: 99.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202840

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBWWH1

Luminous Intensity Polar Plot






TEST NUMBER: P202840

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71
6	82	71	64	59	80	71	64	59	69	63	59		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	54	49	71	61	54	49	59	53	49		58	53	49		57
9	68	57	50	45	67	56	50	45	55	49	45		54	49	45		53
10	64	53	46	42	63	53	46	42	52	46	42		51	45	42		50

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202840

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.0	6.0
10°-20°	496.6	17.8
20°-30°	747.5	26.7
30°-40°	764.3	27.3
40°-50°	464.1	16.6
50°-60°	130.7	4.7
60°-70°	19.9	0.7
70°-80°	6.5	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1411.0	50.4
0°-40°	2175.3	77.8
0°-60°	2770.1	99.0
0°-90°	2796.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2796.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1737	
5°	1744	167
15°	1758	497
25°	1632	747
35°	1239	764
45°	597	464
55°	130	131
65°	18	20
75°	7	6
85°	0	0
90°	0	



TEST NUMBER: P202840

CATALOG NUMBER: LD6B30D010 EU6B30508050 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1737.2
2.5°	1737.2
5°	1744.2
7.5°	1754.8
10°	1754.8
12.5°	1761.8
15°	1758.3
17.5°	1751.2
20°	1726.7
22.5°	1691.6
25°	1631.9
27.5°	1565.2
30°	1474.0
32.5°	1365.2
35°	1238.9
37.5°	1098.5
40°	937.0
42.5°	768.6
45°	596.6
47.5°	442.2
50°	312.3
52.5°	210.6
55°	129.9
57.5°	77.2
60°	38.6
62.5°	24.6
65°	17.5
67.5°	14.0
70°	10.5
72.5°	7.0
75°	7.0
77.5°	3.5
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)