

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204480

Luminaire Tested: **LD6B20D010 EU6B10209040 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6B20D010 EU6B10209040 6LBSB1
Description: PORTFOLIO 6 INCH SHALLOW RECESSED DOWNLIGHT
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1618.6 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204480

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204480

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111		106	106	106		102	102	102
1	111	107	103	100	108	105	101	98		100	98	95		97	94	93		93	91	90
2	102	95	89	84	100	93	88	83		90	85	81		86	83	79		84	80	78
3	94	84	77	72	91	83	76	71		80	74	70		77	73	68		75	71	67
4	86	76	68	62	84	74	67	61		72	65	60		70	64	60		68	63	59
5	80	68	60	54	78	67	59	53		65	58	53		63	57	52		61	56	52
6	74	62	53	47	72	61	53	47		59	52	47		57	51	46		56	50	46
7	69	56	48	42	67	55	48	42		54	47	42		52	46	41		51	45	41
8	64	51	43	38	63	51	43	38		49	42	37		48	42	37		47	41	37
9	60	47	39	34	59	47	39	34		46	39	34		45	38	34		44	38	34
10	56	44	36	31	55	43	36	31		42	36	31		41	35	31		40	35	31

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204480

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	4.2
10°-20°	191.2	11.8
20°-30°	284.4	17.6
30°-40°	331.0	20.4
40°-50°	322.6	19.9
50°-60°	248.1	15.3
60°-70°	137.2	8.5
70°-80°	36.3	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	543.0	33.5
0°-40°	874.0	54.0
0°-60°	1444.8	89.3
0°-90°	1618.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1618.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	714	
5°	710	67
15°	677	191
25°	618	284
35°	531	331
45°	418	323
55°	277	248
65°	138	137
75°	31	36
85°	0	0
90°	0	



TEST NUMBER: P204480

CATALOG NUMBER: LD6B20D010 EU6B10209040 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	714.0
2.5°	714.0
5°	709.9
7.5°	703.7
10°	699.6
12.5°	687.3
15°	677.1
17.5°	666.8
20°	652.4
22.5°	638.1
25°	617.6
27.5°	597.0
30°	576.5
32.5°	554.0
35°	531.4
37.5°	502.7
40°	478.0
42.5°	451.4
45°	418.5
47.5°	387.8
50°	352.9
52.5°	316.0
55°	277.0
57.5°	240.0
60°	205.2
62.5°	170.3
65°	137.5
67.5°	106.7
70°	78.0
72.5°	53.3
75°	30.8
77.5°	14.4
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)